

NBP1-30615**SORCS3 Antibody****Unit Size**

0.5 mg

Concentration

Lyophil

Storage

Store at 4°C short term. Aliquot and store at -20°C long term. Avoid freeze-thaw cycles.

Applications

WB, IHC, IHC-Fr, IHC-P

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

IgG purified

Preservative

No Preservative

Specificity/Sensitivity

Appears to be specific for SORCS3.

Immunogen

A synthetic peptide from the c-terminal region of human SORCS3 (VPS10 domain containing receptor SorCS3) conjugated to an immunogenic carrier protein was used as the immunogen.

Recommended Dilutions

Western Blot 10-50 µg/ml, Immunohistochemistry-Paraffin 10-50 µg/ml, Immunohistochemistry-Frozen 10-50 µg/ml, Immunohistochemistry

Buffer

lyophilized Reconstitute in 500 µl of sterile water. Centrifuge to remove any insoluble material.

Uses

IHC-Paraffin/Frozen, WB. A concentration of 10-50 µg/ml is recommended. The optimal concentration should be determined by the end user. Not yet tested in other applications.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NBP1-30615

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA
 8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com
Novus Canada
 461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com
Novus Europe
 12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com
