
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-26595

NBP1-26595

SMG9 Antibody



Unit Size
0.1 mg

Concentration
1.0 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
IP, WB (-)

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
The immunogen recognized by this antibody maps to a region between residue 75 and 125 of human suppressor with morphogenetic effect on genitalia protein 9 using the numbering given in entry NP_061981.2 (GeneID 56006).

Recommended Dilutions
Immunoprecipitation 5 -10 ug/mg lysate, Western Blot (Negative)

Buffer
Tris-citrate/phosphate buffer, pH 7 to 8

Uses
This antibody is useful for immunoprecipitation. It is not recommended for western analysis.

Images
Immunoprecipitation: SMG9 Antibody [NBP1-26595] - WB analysis of whole cell lysate from HeLa cells using affinity purified rabbit used for IP at 10 mcg/mg lysate. SMG9 was also immunoprecipitated by rabbit anti-SMG9 antibody NBP1-26596.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com