
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-19049

NBP1-19049

Bid Antibody (4D3)



Unit Size
0.1 ml

Concentration
1.0 mg/ml

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ELISA, PAGE

Species
Human

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1 Kappa

Purity
IgG purified

Preservative
0.1% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
BID (4D3)


Immunogen
Recombinant human BID (1-195aa) purified from E. coli

Recommended Dilutions
ELISA, Western Blot 1:1000 - 2000, SDS-Page

Buffer
Phosphate-Buffered Saline (pH 7.4)

Uses
ELISA and Western Blot

Images
Western Blot: Bid Antibody (4D3) [NBP1-19049] The lysates of Jurkat (20ug) were resolved by SDS-PAGE, transferred to NC membrane and probed with anti-human BID (1:1000). Proteins were visualized using a goat anti-mouse secondary antibody con... See more at www.novusbio.com/NBP1-19049



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com