
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-02410

NBP1-02410

Oxytocin Receptor Antibody



Unit Size
0.05 mg

Concentration
Concentrations vary lot to lot. See vial label for concentration.

Storage
Store at 4C short term. Aliquot and store at -80C long term. Avoid freeze-thaw cycles.

Applications
ELISA, IHC, IHC-P

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.1% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
N-terminal extracellular domain of human


Immunogen
Synthetic 20 amino acid peptide corresponding to N-terminal extracellular domain of human Oxytocin Receptor.

Recommended Dilutions
ELISA, Immunohistochemistry, Immunohistochemistry-Paraffin 20 ug/ml

Buffer
PBS

Uses
Immunohistochemistry-Paraffin: Use heat induced antigen retrieval in pH 6.0 citrate buffer.

Images
Immunohistochemistry-Paraffin: Oxytocin Receptor Antibody [NBP1-02410] - Staining of human pregnant uterus. Immunohistochemistry of formalin-fixed, paraffin-embedded tissue after heat-induced antigen retrieval. Antibody concentration 20 ug/m... See more at www.novusbio.com/NBP1-02410



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com