

NBP1-02993**TLR1 Antibody****Unit Size**

0.05 mg

Concentration

Concentrations vary lot to lot. See vial label for concentration.

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, IHC, IHC-P

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

Ion exchange chromatography

Preservative

0.02% Sodium Azide

Specificity/Sensitivity

peptide corresponding to 16 amino acids near the amino terminus of human TLR1

Immunogen

Peptide corresponding to 16 amino acids near the amino terminus of human TLR1

Recommended Dilutions

Immunohistochemistry, Immunohistochemistry-Paraffin 5 ug/ml, Western Blot 1-2 ug/ml

Buffer

PBS

Uses

This antibody is useful for the following applications and at the following dilutions: Western Blot 1-2 ug/ml, Immunohistochemistry-Paraffin 5 ug/ml.

Images

Immunohistochemistry-Paraffin: TLR1 Antibody [NBP1-02993] - Staining of human small intestine. Immunohistochemistry of formalin-fixed, paraffin-embedded tissue after heat-induced antigen retrieval. Antibody concentration 5 ug/ml.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

