
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-54383

NBP1-54383

EEF2 Antibody



Unit Size
0.05 mg

Concentration
Lyoph

Storage
Store at -20C. Avoid freeze-thaw cycles.

Applications
WB, IHC-P

Species
Human, Mouse, Rat, C. elegans, Drosophila

Host
Rabbit

Clonality
Polyclonal

Purity
Peptide affinity purified

Preservative
No Preservative

Updated 3/9/2013 2.0

Immunogen
Synthetic peptides corresponding to EEF2(eukaryotic translation elongation factor 2) The peptide sequence was selected from the N terminal of EEF2. Peptide sequence TDSLVCKAGIIASARAGETRFTDTRKDEQERCITIKSTAISLFYELSEND.


Recommended Dilutions
Immunohistochemistry-Paraffin, Western Blot

Buffer
PBS & 2% Sucrose lyophilized with the antibody.Centrifuge the vial of lyoph antibody at 12,000 x g for 20 seconds. Add 50ul of distilled water. Vortex followed by centrifuge again to pellet the solution.Final concentration is 1 mg/ml in PBS buffer


Uses
This is a rabbit polyclonal antibody against EEF2 and was validated on Western blot.

Images

Western Blot: EEF2 Antibody [NBP1-54383] - Titration: 0.2-1 ug/ml, Positive Control: Hela cell lysate.



Immunohistochemistry-Paraffin: EEF2 Antibody [NBP1-54383] - Human small intestine tissue at an antibody concentration of 5 ug/ml.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com