
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-03166

NBP1-03166

TIP120B Antibody



Unit Size
0.05 ml

Concentration
Concentrations vary lot to lot. See vial label for concentration.

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, ELISA, IHC, IHC-P, IP

Species
Human, Mouse, Rat

Host
Rabbit

Clonality
Polyclonal

Purity
Delipidation and Defibrination

Preservative
0.01% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
Amino acids 1130-1143 of Human CAND2/TIP120B (C-terminal) coupled to KLH.

Immunogen
Synthetic peptide corresponding to Amino acids 1130-1143 of Human CAND2/TIP120B (C-terminal) coupled to KLH

Recommended Dilutions
ELISA 1:2000-1:10000
Immunohistochemistry
Immunohistochemistry-Paraffin 1:500
Immunoprecipitation
Western Blot 1:500-1:1000

Buffer
PBS

Uses
This antibody is useful for the following applications and at the following dilutions: Western Blot 1:500-1:1000, immunoprecipitation, ELISA 1:2000-1:10000, Immunohistochemistry-Paraffin 1:500

Images
Immunohistochemistry-Paraffin: TIP120B Antibody [NBP1-03166] - Staining of human kidney. Immunohistochemistry of formalin-fixed, paraffin-embedded tissue after heat-induced antigen retrieval. Antibody dilution 1:500.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com