
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-51570

NBP1-51570

REG1 Antibody (1A4)



Unit Size
0.1 ml

Concentration
This product is unpurified. The exact concentration of antibody is not quantifiable.

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
ELISA, ICC/IF

Species
Human

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1

Purity
Ascites

Preservative
0.03% Sodium Azide

Updated 3/9/2013 2.0

Immunogen
Purified recombinant fragment of human REG1A fused with hIgGFc tag expressed in HEK293 cell line.


Recommended Dilutions
ELISA 1:10000, Immunocytochemistry/Immunofluorescence 1:200 - 1:1000

Buffer
Ascitic fluid containing 0.03% sodium azide.


Uses
This antibody is useful in ELISA, Immunofluorescence.

Images

Immunohistochemistry-Paraffin: REG1 Antibody (1A4) [NBP1-51570] - Immunohistochemical analysis of paraffin-embedded human Pancreas tissues using REG1A mouse mAb



Immunofluorescence: REG1 Antibody (1A4) [NBP1-51570] - Confocal immunofluorescence analysis of PC12 cells using REG1A mouse mAb (green). Blue: DRAQ5 fluorescent DNA dye.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com