
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBP1-48049

NBP1-48049

USP38 Antibody (1D11)



Unit Size
0.1 ml

Concentration
0.55 mg/ml

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB

Species
Human

Host
Mouse

Clonality
Monoclonal

Isotype
IgM

Purity
Affinity purified

Preservative
0.02% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
This antibody is specific for Homo sapiens ubiquitin specific peptidase 38 (USP38).


Immunogen
Protein expressed in 293T cell transfected with human USP38 expression vector

Recommended Dilutions
Western Blot 1:1000-2000

Buffer
PBS (pH 7.3) containing 1% BSA, 50% glycerol

Images

Western Blot: USP38 Antibody (1D11) [NBP1-48049] Analysis of extracts (35ug) from 9 different cell lines by using anti-USP38 monoclonal antibody.



Western Blot: USP38 Antibody (1D11) [NBP1-48049] - HEK293T cells were transfected with the pCMV6-ENTRY control (Left lane) or pCMV6-ENTRY USP38 (Right lane) cDNA for 48 hrs and lysed. Equivalent amounts of cell lysates (5 ug per lane) were s... See more at www.novusbio.com/NBP1-48049



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com