

NBP1-30429**BRCC3 Antibody (AT3B1)****Unit Size**

0.1 ml

Concentration

Please see the vial label for concentration.

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB, ELISA

Species

Human

Host

Mouse

Clonality

Monoclonal

Isotype

IgG1 Kappa

Purity

Affinity purified

Preservative

0.1% Sodium Azide

Specificity/Sensitivity

This antibody is specific for BRCC36 mAb, clone AT3B1, is derived from hybridization of mouse F0 myeloma cells with spleen cells from BALB/c mice immunized with a recombinant human BRCC36 protein.

Immunogen

Recombinant BRCC36 (1-316aa) purified from E. coli

Recommended Dilutions

ELISA, Western Blot 1:1000-1:2000

Buffer

Phosphate-Buffered Saline (pH 7.4)

Uses

The antibody has been tested by ELISA and Western blot analysis to assure specificity and reactivity. Since application varies, however, each investigation should be titrated by the reagent to obtain optimal results. Recommended dilution range for Western blot analysis is 1:1000-1:2000.

Images

Western Blot: BRCC3 Antibody (AT3B1) [NBP1-30429] - Cell lysates of HeLa(20ug) were resolved by SDS-PAGE, transferred to NC membrane and probed with anti-human BRCC36 (1:1000). Proteins were visualized using a goat anti-mouse secondary antib... See more at www.novusbio.com/NBP1-30429



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

