

**NBP1-04355****Von Hippel Lindau Antibody (52A11)****Unit Size**

0.1 ml

**Concentration**

1.0 mg/ml

**Storage**

Store at 4°C short term. Aliquot and store at -20°C long term. Avoid freeze-thaw cycles.

**Applications**

WB, ELISA

**Species**

Human

**Host**

Mouse

**Clonality**

Monoclonal

**Isotype**

IgG2b

**Purity**

Protein G purified

**Preservative**

0.1% Sodium Azide

**Specificity/Sensitivity**

Anti-human VHL mAb, clone 52A11, is derived from hybridization of mouse SP2/O myeloma cells with spleen cells from BALB/c mice immunized with a recombinant human His-VHL protein.

**Immunogen**

Recombinant human His-VHL (1-154 aa) purified from E. coli

**Recommended Dilutions**

ELISA, Western Blot 1:500-1:1000

**Buffer**

Phosphate-Buffered Saline (pH 7.4)

**Uses**

The antibody has been tested by ELISA and Western blot analysis to assure specificity and reactivity.

**Images**

Western Blot: Von Hippel Lindau Antibody (52A11) [NBP1-04355] HepG2 cell lysate was resolved by SDS-PAGE, transferred to PVDF membrane and probed with anti-human VHL antibody (1:500). Protein was visualized using a goat anti-mouse secondary ... See more at [www.novusbio.com/NBP1-04355](http://www.novusbio.com/NBP1-04355)



Updated 3/9/2013 2.0

**Limitations:** This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit [www.novusbio.com/guarantee](http://www.novusbio.com/guarantee).**

**Novus USA**

8100 Southpark Way, A-8  
 Littleton, CO 80120  
 p) 888-506-6887  
 p) 303-730-1950  
 f) 303-730-1966  
[novus@novusbio.com](mailto:novus@novusbio.com)

**Novus Canada**

461 North Service Road West,  
 Unit B37  
 Oakville, ON L6M 2V5  
 p) 855-668-8722  
 f) 905-827-6402  
[canada@novusbio.com](mailto:canada@novusbio.com)

**Novus Europe**

12 Cambridge Science Park  
 Cambridge, UK CB4 0FQ  
 UK: p) +44-1223-426-001, f) +44-871-971-1635  
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79  
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340  
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31  
[europe@novusbio.com](mailto:europe@novusbio.com)

