
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com
Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NBL1-08948

NBL1-08948

CD40 Overexpression Lysate



Unit Size
0.1 mg

Storage
Store at -80C. Avoid freeze-thaw cycles.

Applications
WB

Molecular Weight
28.4kDa

Purity
Protein

Updated 3/9/2013 2.0

Specificity/Sensitivity
Homo sapiens CD40 molecule, TNF receptor superfamily member 5 (CD40), transcript variant 1, mRNA.


Immunogen
The lysate was created in HEK293T cells, using plasmid ID RC201977 and based on accession number NM_001250. The protein contains a C-terminal DDK tag.

Recommended Dilutions
Western Blot

Buffer
RIPA buffer

Uses
This product is intended for use as a positive control in Western Blot. You will receive the lysate (100ug), and an empty vector negative control (100 ug).

Images
Western Blot: CD40 Overexpression Lysate (Adult Normal) [NBL1-08948] Left-Empty vector transfected control cell lysate (HEK293 cell lysate); Right -Over-expression Lysate for CD40.



Notes
This product is manufactured by and sold under license from OriGene Technologies and its use is limited solely for research purposes. Please note that “1 mg/ml” refers to the total protein concentration and that the specific protein concentration is not determined at this time.

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com