
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB600-975

NB600-975

TAX1BP1 Antibody



Unit Size
0.1 mg

Concentration
0.5 mg/ml

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB

Species
Human, Mouse, Rat

Host
Rabbit

Clonality
Polyclonal

Purity
Protein G purified

Preservative
0.05% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
Researchers are encouraged to titer for their specific applications.


Immunogen
This antibody was developed against a portion of amino acids 700-800 of human Traf6BP (Genbank Accession No. AF268075). The sequence used is 94% homologous in mouse.

Recommended Dilutions
Western Blot 2 ug/ml

Buffer
PBS containing 0.2% gelatin

Uses
In Western Blot detects a band of approximately 86 kDa.

Images
Western Blot: TRAF6BP Antibody [NB600-975] - Western blot analysis of TRAF6BP using NB600-975 at 2 ug/ml dilution against 20 ug of Raji cells.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com