
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB500-201R

NB500-201R

Survivin Antibody [DyLight 550]



Unit Size
0.05 ml

Concentration
1.0 mg/ml

Storage
Store at 4C in the dark.

Applications
WB, ICC/IF, IHC, IHC-P, IP

Species
Human, Mouse, Rat, Canine, Feline

Host
Rabbit

Clonality
Polyclonal

Conjugate
DyLight 550

Purity
Affinity purified

Preservative
No Preservative

Marker
Astrocyte Marker

Updated 3/9/2013 2.0

Specificity/Sensitivity
This is specific for survivin.

Immunogen
Full-length recombinant human survivin.

Recommended Dilutions
Immunoprecipitation, Western Blot 1 ug/ml, Immunohistochemistry-Paraffin 0.5 ug/ml, Immunocytochemistry/Immunofluorescence, Immunohistochemistry

Buffer
50mM sodium borate

Uses
By Western blot, this antibody recognizes a band at ~16.5 kDa representing survivin. Immunohistochemistry with cytoplasmic and nuclear detection of survivin can be achieved using formalin-fixed paraffin-embedded tissue sections with prior antigen retrieval (pressure cooking).

Images
This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB500-201R

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com