

NB500-156**TFII-I Antibody****Unit Size**

0.1 ml

Concentration

1.0 mg/ml

Storage

Store at 4°C. Do not freeze.

Applications

WB

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

Immunogen affinity purified

Preservative

0.1% Sodium Azide

Immunogen

A synthetic peptide, which represented a portion of human general transcription factor II-I encoded within exons 27 and 28 (LocusLink ID 2969).

Recommended Dilutions

Western Blot

Buffer


Tris-citrate/phosphate buffer, pH 7 to 8

Uses

By Western Blot, this antibody recognizes a band at ~135 kDa, representing TFII-I. *The investigator should determine the optimal working dilution for a specific application.

Images

Western Blot: TFII-I Antibody [NB500-156] - Whole cell lysate (100 ug) from HEK293 cells treated with GTF2I/TFII-I siRNA (+) or untreated (-). Antibody used at 0.2 ug/ml.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

