
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB120-15248

NB120-15248

Vimentin Antibody



Unit Size
0.5 ml

Concentration
0.2 mg/ml

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB, IHC, IHC-P

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
Sodium Azide

Marker
Neuronal Stem Cell Marker, Cytoskeleton-Intermediate Filaments Marker

Updated 3/9/2013 2.0

Specificity/Sensitivity
Vimentin

Immunogen
Recombinant full length protein (Human).


Recommended Dilutions
Western Blot, Immunohistochemistry-Paraffin, Immunohistochemistry

Buffer
Constituents: BSA, 10mM PBS. pH 7.4

Uses
IHC-P: Antigen retrieval is not essential but may optimise staining. WB: Predicted molecular weight: 56 kDa.

References
Dai G, Freudenberger T, Zipper P, et al. Chronic Ultraviolet B Irradiation Causes Loss of Hyaluronic Acid from Mouse Dermis Because of Down-Regulation of Hyaluronic Acid Synthases. Am J Pathol, 2007;171(5):1451-61. 2007 November 1. [PMID: 17982124] (IHC

Images
Formalin fixed paraffin embedded human melanoma stained with Vimentin antibody.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com