

NB100-56410**DUSP8 Antibody****Unit Size**

0.1 mg

Concentration

0.5 mg/ml

Storage

Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications

WB

Species

Human

Host

Rabbit

Clonality

Polyclonal

Purity

Protein G purified

Preservative

0.05% Sodium Azide

Specificity/Sensitivity

The NCBI accession number for DUSP8 is NP_004411. The amino acid sequence used as immunogen has 100% identity in human, mouse and rat.

Immunogen

A portion of amino acids 250-300 of human DUSP8 were used as the immunogen.

Recommended Dilutions

Western Blot

Buffer


PBS containing 0.2% gelatin

Uses

WB: 1-3 ug/ml

Images

Western Blot: DUSP8 Antibody [NB100-56410] -
 Western blot analysis of DUSP8 in HeLa cell lysate
 using NB100-56410 at 2 ug/ml.



Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

