

NB100-519G**OS9 Antibody [DyLight 488]****Unit Size**

0.1 ml

Concentration

1.0 mg/ml

Storage

Store at 4C in the dark.

Applications

WB, ICC/IF, IHC, IHC-P, IP

Species

Human, Mouse

Host

Rabbit

Clonality

Polyclonal

Conjugate

DyLight 488

Purity

Affinity purified

Preservative

No Preservative

Specificity/Sensitivity

This is specific for isoforms 1 and 2 of human OS-9.

Immunogen

Synthetic peptide made to an internal portion of isoform 1 of the human protein (within residues 300-400). [Swiss-Prot# Q13438]

Recommended Dilutions

immunohistochemistry 0.5-1.0 ug/ml, immunofluorescence 0.2-1.0 ug/ml, immunoprecipitation, Western Blot 0.2-1.0 ug/ml, Immunohistochemistry-Paraffin 1:100-1:250

Buffer

50mM sodium borate

Uses

This antibody is useful in Western blot, where bands can be seen ~75 kDa representing isoform 1 and ~70 kDa representing isoform 2. This antibody is also useful for immunofluorescence, immunohistochemistry, and immunoprecipitation.

ImagesThis product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-519G

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. For more information on our guarantee, please visit www.novusbio.com/guarantee.

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

