
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB600-548

NB600-548

VEGF Antibody (5C3.F8)



Unit Size
0.5 ml

Concentration
Concentrations vary lot to lot. See vial label for concentration.

Storage
Store at 4C. Do not freeze.

Applications
WB, IHC, IHC-P

Species
Human, Mouse

Molecular Weight
27kDa

Host
Mouse

Clonality
Monoclonal

Isotype
IgG1 Kappa

Purity
Protein G purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
VEGF (5C3.F8)

Immunogen
Human VEGF from a glioma.

Recommended Dilutions
Western Blot 1-2ug/ml, Immunohistochemistry-Paraffin 1/50, Immunohistochemistry

Buffer
10mM PBS [pH7.4] with 0.2% BSA

Uses
This antibody can be used in Immunohistochemistry-FFPE and Western Blot. By Western blot, this antibody detects a band of 19-22 kDa (reduced), which corresponds to the predicted molecular weight of VEGF. Not tested in other applications. Optimal dilutions should be determined by the end user.

References (more available at www.novusbio.com/NB600-548)
Harasawa M, Yasuda M, Hirasawa T et al Analysis of mTOR inhibition-involved pathway in ovarian clear cell adenocarcinoma Acta Histochem Cytochem 2011 Apr 28 [PMID: 21614172] (WB, Human

Images
Western Blot: VEGF Antibody (5C3.F8) [NB600-548] - Western Blot analysis of VEGF from Human Cells in a reducing gel.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com