

NB100-109H**MTH1 Antibody [HRP]****Unit Size**

0.2 ml

Concentration

Please see the vial label for concentration.

Storage

Store at 4°C in the dark.

Applications

WB, IHC, IHC-Fr

Species

Human, Mouse, Rat

Host

Rabbit

Clonality

Polyclonal

Conjugate

HRP

Purity

Affinity purified

Preservative

No Preservative

Specificity/Sensitivity

NB100-109 is specific for MTH1.

Immunogen

A c-terminal peptide derived from the human MTH1 conjugated to KLH.

Recommended Dilutions

Western Blot, Immunohistochemistry-Frozen, Immunohistochemistry

Buffer

PBS

Uses

This antibody is useful for Western blot detection of MTH1 where a band is seen at ~18kDa. This antibody is also useful for immunohistochemistry on frozen sections.

Images

This product does not currently have an image. Earn rewards by submitting your image of this product. Submit a review with your image here: www.novusbio.com/NB100-109H

Updated 3/9/2013 2.0

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. **For more information on our guarantee, please visit www.novusbio.com/guarantee.**

Novus USA

8100 Southpark Way, A-8
 Littleton, CO 80120
 p) 888-506-6887
 p) 303-730-1950
 f) 303-730-1966
novus@novusbio.com

Novus Canada

461 North Service Road West,
 Unit B37
 Oakville, ON L6M 2V5
 p) 855-668-8722
 f) 905-827-6402
canada@novusbio.com

Novus Europe

12 Cambridge Science Park
 Cambridge, UK CB4 0FQ
 UK: p) +44-1223-426-001, f) +44-871-971-1635
 DE: p) +49-6922-22340-60, f) +49-0800-58926-79
 IT: p) +39-02-4032-6786, f) +39-02-4032-6340
 FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com

