
NB200-200

Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB200-200

NB200-200

TSC2 Antibody



Unit Size
0.1 mg

Concentration
1.0 mg/ml

Storage
Store at 4C. Do not freeze.

Applications
IP, WB (-)

Species
Human

Host
Rabbit

Clonality
Polyclonal

Purity
Immunogen affinity purified

Preservative
0.09% Sodium Azide

Updated 3/9/2013 2.0


Immunogen
The immunogen recognized by this antibody maps to a region between residues 1 and 50 of human Tuberous Sclerosis 2 using the numbering given in Swiss-Prot entry P49815 (GeneID 7249).

Recommended Dilutions
Immunoprecipitation 2 -5 ug/mg lysate, Western Blot (Negative)

Buffer
Tris-citrate/phosphate buffer, pH 7 to 8

Uses
Optimal working dilutions should be determined experimentally by the investigator. Prepare working dilution immediately before use. In some cases, the antibody may be diluted further than indicated.

Images



Immunoprecipitation: TSC2 Antibody [NB200-200] - Immunoprecipitation of Human TSC2 and Co-Immunoprecipitation of Human TSC1. Samples: Whole cell lysate (1 mg/IP; 1/4 of IP reaction loaded) from HeLa cells. Antibodies: Affinity purified r... See more at www.novusbio.com/NB200-200

Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com