
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-302

NB100-302

NTH1 Antibody



Unit Size
0.1 ml

Concentration
This product is unpurified. The exact concentration of antibody is not quantifiable.

Storage
Aliquot and store at -20C or -80C. Avoid freeze-thaw cycles.

Applications
WB

Species
Human

Molecular Weight
37kDa

Host
Rabbit

Clonality
Polyclonal

Purity
Whole antisera

Preservative
0.1% Sodium Azide


Updated 3/9/2013 2.0

Immunogen
Full-length recombinant human NTH1. [UniProt# P78549]

Recommended Dilutions
Western Blot 1:1000-1:5000

Uses
This NTH1 antibody is useful for Western blot, where a band at ~37 kD.

Images
Western Blot: NTH1 Antibody [NB100-302] - Analysis of A549 cells using NB100-302. A band is seen at 35 kDa representing NTH1.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com