9F, No. 108, Jhouzih St.,Taipei, Taiwan
Tel: + 886-2-8751-1888 Fax: + 886-2-6602-1218
E-mail: sales@abnova.com

Datasheet

RHOA monoclonal antibody (M04), clone 1B12

Catalog Number: H00000387-M04

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody raised against a full length recombinant RHOA.

Clone Name: 1B12

Immunogen: RHOA (AAH01360, 1 a.a. ~ 193 a.a) full-length recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.

Sequence:
MAAIRKKLVIVGDGACGKTCLLIVFSKDQFPEVYVPTVF
ENYVADIEVDGKQVELALWDTAGQEDYDRLRPLSYPD
TDVILMCFSIDSPDSLENIPEKWTPEVKHFCPNVPIILVG
NKKDLRNDEHTRRELAKMKQEPVKPEEGRDMANRIG
AFGYMECSAKTKDGVREVFEMATRAALQARRGKKKS
GCLVL

Host: Mouse

Reactivity: Human

Applications: ELISA, IF, IHC-P, S-ELISA, WB-Ce, WB-Re, WB-Tr
(See our web site product page for detailed applications information)

Protocols: See our web site at http://www.abnova.com/support/protocols.asp or product page for detailed protocols

Isotype: IgG1 lambda

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 387

Gene Symbol: RHOA

Gene Alias: ARH12, ARHA, RHO12, RHOH12

References:

1. Relationship of RhoA signaling activity with ezrin expression and its significance in the prognosis for breast cancer patients. Ma L, Liu YP, Zhang XH, Geng CZ, Li ZH. Chin Med J (Engl). 2013 Jan;126(2):242-7.