

Datasheet

CHODL monoclonal antibody (M03), clone 1A5

pathogens. This protein localizes predominantly to the perinuclear region. [provided by RefSeq]

Catalog Number: H00140578-M03

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody raised against a partial recombinant CHODL.

Clone Name: 1A5

Immunogen: CHODL (NP_079220, 23 a.a. ~ 94 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.

Sequence:

RVVSGQKVCFADFKHPCYKMAYFHELSSRVSFQEARL
ACESEGGVLLSLENEAEQKLIESMLQNLTKPGTGI

Host: Mouse

Reactivity: Human

Applications: ELISA, S-ELISA, WB-Re

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Isotype: IgG2a Kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 140578

Gene Symbol: CHODL

Gene Alias: C21orf68, FLJ12627, MT75, PRED12

Gene Summary: This gene encodes a type I membrane protein with a carbohydrate recognition domain characteristic of C-type lectins in its extracellular portion. In other proteins, this domain is involved in endocytosis of glycoproteins and exogenous sugar-bearing