9F, No. 108, Jhouzih St., Taipei, Taiwan
Tel: + 886-2-8751-1888 Fax: + 886-2-6602-1218
E-mail: sales@abnova.com

Datasheet

DYNLL2 polyclonal antibody (A01)

Catalog Number: H00140735-A01

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a partial recombinant DYNLL2.

Immunogen: DYNLL2 (NP_542408, 1 a.a. ~ 72 a.a) partial recombinant protein with GST tag.

Sequence:
MSDRKAVIKNADMSEDMQQDAVDCATQAMEKYNIEK
DIAAYIKKEFDKKYNPTWHCIVGRNFGSYVTHETKH

Host: Mouse

Reactivity: Human

Applications: ELISA, WB-Ce, WB-Re
(See our web site product page for detailed applications information)

Protocols: See our web site at http://www.abnova.com/support/protocols.asp or product page for detailed protocols

Storage Buffer: 50 % glycerol

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 140735

Gene Symbol: DYNLL2

Gene Alias: DNCL1B, Dlc2, MGC17810

References:
1. Different microtubule motors move early and late endocytic compartments. Loubery S, Wilhelm C, Hurbain I, Neveu S, Louvard D, Coudrier E. Traffic. 2008 Apr;9(4):492-509. Epub 2008 Jan 10.