
Orders: orders@novusbio.com
Support: technical@novusbio.com
Web: www.novusbio.com

Protocols, Publications, Related Products, Reviews and more:
www.novusbio.com/NB100-56441

NB100-56441

EB3 Antibody



Unit Size
0.1 mg

Concentration
0.5 mg/ml

Storage
Store at 4C short term. Aliquot and store at -20C long term. Avoid freeze-thaw cycles.

Applications
WB

Species
Human, Mouse, Rat

Host
Rabbit

Clonality
Polyclonal

Purity
Protein G purified

Preservative
0.05% Sodium Azide

Updated 3/9/2013 2.0

Specificity/Sensitivity
In human brain, an approx. 38 kDa band is observed.


Immunogen
This antibody was developed against a synthetic peptide to a portion of the human EB3 protein.

Recommended Dilutions
Western Blot 0.5-2 ug/ml

Buffer
PBS containing 0.2% gelatin

Uses
Western Blot

Images
Western Blot: EB3 Antibody [NB100-56441] - Western blot analysis of EB3 using NB56441 on 15 ugs of human brain lysate.



Limitations: This product is for research use only and is not approved for use in humans or in clinical diagnosis. Products are guaranteed for six months from the date of receipt except for peptides and proteins which are guaranteed for 3 months. ***For more information on our guarantee, please visit www.novusbio.com/guarantee.***

Novus USA
8100 Southpark Way, A-8
Littleton, CO 80120
p) 888-506-6887
p) 303-730-1950
f) 303-730-1966
novus@novusbio.com

Novus Canada
461 North Service Road West,
Unit B37
Oakville, ON L6M 2V5
p) 855-668-8722
f) 905-827-6402
canada@novusbio.com

Novus Europe
12 Cambridge Science Park
Cambridge, UK CB4 0FQ
UK: p) +44-1223-426-001, f) +44-871-971-1635
DE: p) +49-6922-22340-60, f) +49-0800-58926-79
IT: p) +39-02-4032-6786, f) +39-02-4032-6340
FR: p) +33-1-76-77-45-30, f) +33-1-76-77-45-31
europe@novusbio.com