

Datasheet

NEK10 purified MaxPab mouse polyclonal antibody (B01P)

Catalog Number: H00152110-B01P

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a full-length human NEK10 protein.

Immunogen: NEK10 (NP_001026911.1, 1 a.a. ~ 474 a.a) full-length human protein.

Sequence:

MVPVQPAEPPEVLKSEPYGEKADVWAVGCILYQMATL
SPPFYSTNMLSLATKIVEAVYEPVPEGIYSEKVTDTISR
CLTPDAEARPDIVEVSSMISDVMMKYLDNLSTSQLSLE
KKLERERRRTQRYFMEANRNTVTCHHELAVLSHETFE
KASLSSSSSGAASLKSELSADLPPEGFQASYGKDE
DRACDEILSDDNFNLENAEKDTYSEVDELDISDNSSS
SSSSPLKESTFNILKRSFSASGGERQSQTRDFTGGTG
SRPRPALLPLDLLLKVPPHMLRAHIKEIAELVTGWQS
HSLPAVILRNLDHASAGIAVSQRKVRQISDPIQQILQL
HKIYITQLPPALHHNLKRRVIERFKKSLFSQQSNPCNL
KSEIKKLSQGSPEPIEPNFFTADYHLLHRSSGGNSLSP
NDPTGLPTSIELEEGITYEQMQTVIEEVLEESGYYNFTS
NRYHSYPWGTKNHPTKR

Host: Mouse

Reactivity: Human

Applications: WB-Tr

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 152110

Gene Symbol: NEK10

Gene Alias: FLJ32685