

Datasheet

APOBEC3H purified MaxPab mouse polyclonal antibody (B01P)

Catalog Number: H00164668-B01P

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a full-length human APOBEC3H protein.

Immunogen: APOBEC3H (AAH69023.1, 1 a.a. ~ 182 a.a) full-length human protein.

Sequence:

MALLTAETFRLQFNNKRRLRRPYYPKALLCYQLTPQ
NGSTPTRGYFENKKKCHAEICFINEIKSMGLDETQCYQ
VTCYLTWSPCSSCAWELVDFIKAHDHLNLGIFASRLYY
HWCKPQQKGLRLLCGSQVPVEVMGFPEFADCWENF
VDHEKPLSFNPYKMLEELDKNSRAIKRRLERIKS

Host: Mouse

Reactivity: Human

Applications: IF, WB-Ti, WB-Tr

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 164668

Gene Symbol: APOBEC3H

Gene Alias: ARP10, dJ742C19.2

Gene Summary: Members of the APOBEC family of proteins, like APOBEC3H, are mRNA editing enzymes that affect protein diversity by deamination of cytidine to produce uridine (Wedekind et al., 2003 [PubMed 12683974]).[supplied by OMIM]