

Datasheet

TRIM49 monoclonal antibody (M03), clone 3H8

[provided by RefSeq]

Catalog Number: H00057093-M03

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody
raised against a partial recombinant TRIM49.

Clone Name: 3H8

Immunogen: TRIM49 (NP_065091, 251 a.a. ~ 340 a.a)
partial recombinant protein with GST tag. MW of the
GST tag alone is 26 KDa.

Sequence:

ILHRSESVLLHMPQPLNPELSAGPITGLRDRLNQFRVHI
TLHHEEANNDIFLYEILRSMCIGCDHQDVPYFTATPRS
FLAWGVQTFTSGK

Host: Mouse

Reactivity: Human

Applications: ELISA, S-ELISA, WB-Ce, WB-Re
(See our web site product page for detailed applications
information)

Protocols: See our web site at
<http://www.abnova.com/support/protocols.asp> or product
page for detailed protocols

Isotype: IgG2a Kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to
avoid repeated freezing and thawing.

Entrez GeneID: 57093

Gene Symbol: TRIM49

Gene Alias: RNF18

Gene Summary: The protein encoded by this gene
contains a RING zinc finger, a motif known to be
involved in protein-protein interactions. This gene has
been found to be preferentially expressed in testis.