

## Datasheet

### ENO2 monoclonal antibody, clone 171

**Catalog Number:** MAB6784

**Regulation Status:** For research use only (RUO)

**Product Description:** Mouse monoclonal antibody raised against recombinant ENO2.

**Clone Name:** 171

**Immunogen:** Recombinant protein corresponding to human ENO2.

**Host:** Mouse

**Reactivity:** Human

**Applications:** ELISA

(See our web site product page for detailed applications information)

**Protocols:** See our web site at <http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Specificity:** This antibody reacts with recombinant human ENO2.

**Form:** Lyophilized

**Isotype:** IgG1, kappa

**Recommend Usage:** The optimal working dilution should be determined by the end user.

**Storage Buffer:** Lyophilized from 10 mM PBS, pH 7.2

**Storage Instruction:** Store at -20°C.  
Aliquot after reconstitution to avoid repeated freezing and thawing.

**Entrez GeneID:** 2026

**Gene Symbol:** ENO2

**Gene Alias:** NSE

**Gene Summary:** This gene encodes one of the three

enolase isoenzymes found in mammals. This isoenzyme, a homodimer, is found in mature neurons and cells of neuronal origin. A switch from alpha enolase to gamma enolase occurs in neural tissue during development in rats and primates. [provided by RefSeq]