

## Datasheet

### FFAR2 polyclonal antibody

**Catalog Number:** PAB16401

**Regulation Status:** For research use only (RUO)

**Product Description:** Rabbit polyclonal antibody raised against synthetic peptide of FFAR2.

**Immunogen:** A synthetic peptide (conjugated with KLH) corresponding to human FFAR2.

**Host:** Rabbit

**Reactivity:** Gorilla, Human

**Applications:** IHC-P

(See our web site product page for detailed applications information)

**Protocols:** See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Specificity:** C-terminal domain of human.

**Form:** Liquid

**Purification:** Immunoaffinity purification

**Recommend Usage:** Immunohistochemistry

(Formalin/PFA-fixed paraffin-embedded sections) (15 ug/mL)

The optimal working dilution should be determined by the end user.

**Storage Buffer:** In PBS (0.1% sodium azide)

**Storage Instruction:** Store at 4°C. For long term storage store at -80°C.

Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 2867

**Gene Symbol:** FFAR2

**Gene Alias:** FFA2R, GPR43

**Gene Summary:** This gene encodes a member of the GP40 family of G protein-coupled receptors that are

clustered together on chromosome 19. The encoded protein is a receptor for short chain free fatty acids and may be involved in the inflammatory response and in regulating lipid plasma levels. [provided by RefSeq]