

Datasheet

TNFRSF19L monoclonal antibody (M01), clone 3F8

Catalog Number: H00084957-M01

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody raised against a partial recombinant TNFRSF19L.

Clone Name: 3F8

Immunogen: TNFRSF19L (NP_116260, 26 a.a. ~ 124 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.

Sequence:

STTLWQCPPGEEPDLDPGQGTLCRPCPPGTFSAAWG
SSPCQPHARCSLWRRLEAQVGMATRD TLCGDCWPG
WFGPWGVPRVPCQPCSWAPLGTHGCDEW

Host: Mouse

Reactivity: Human

Applications: ELISA, RNAi-Ab, S-ELISA, WB-Re, WB-Tr
(See our web site product page for detailed applications information)

Protocols: See our web site at
<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Isotype: IgG2a Kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 84957

Gene Symbol: RELT

Gene Alias: FLJ14993, TNFRSF19L

Gene Summary: The protein encoded by this gene is a member of the TNF-receptor superfamily. This receptor is especially abundant in hematologic tissues. It has

been shown to activate the NF-kappaB pathway and selectively bind TNF receptor-associated factor 1 (TRAF1). This receptor is capable of stimulating T-cell proliferation in the presence of CD3 signaling, which suggests its regulatory role in immune response. Two alternatively spliced transcript variants of this gene encoding the same protein have been reported. [provided by RefSeq]