

Datasheet

ANXA8 polyclonal antibody (A01)

Catalog Number: H00000244-A01

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a partial recombinant ANXA8.

Immunogen: ANXA8 (NP_001621, 228 a.a. ~ 326 a.a) partial recombinant protein with GST tag.

Sequence:

IEDSIKSETHGSLEEAMLTVVKCTQNLHSYFAERLYYA
MKGAGTRDGTLRNIVSRSEIDLNLKCHFKKMYGKTL
SMIMEDTSGDYKNALLSLVGSD

Host: Mouse

Reactivity: Human

Applications: ELISA, WB-Re

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: 50 % glycerol

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 244

Gene Symbol: ANXA8L2

Gene Alias: ANXA8, FLJ32754, FLJ54151, bA145E20.2

Gene Summary: This gene encodes a member of the annexin family of evolutionarily conserved Ca²⁺ and phospholipid binding proteins. The encoded protein may function as an anticoagulant that indirectly inhibits the thromboplastin-specific complex. Overexpression of this gene has been associated with acute myelocytic leukemia. A highly similar duplicated copy of this gene is found in close proximity on the long arm of chromosome 10. [provided by RefSeq]