9F, No. 108, Jhouzih St.,Taipei, Taiwan
Tel: + 886-2-8751-1888 Fax: + 886-2-6602-1218
E-mail: sales@abnova.com

Datasheet

AOAH purified MaxPab mouse polyclonal antibody (B01P)

Catalog Number: H00000313-B01P

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a full-length human AOAH protein.

Immunogen: AOAH (NP_001628.1, 1 a.a. ~ 575 a.a) full-length human protein.

Sequence:
MQSPWKILTVAPLFLLLSLQSSASPANDDQSRPSLSN
GHTCVGCVLVVSVIEQLAQVHNSTVQASMERLCSYLP
EKLFLKTTCYLVIDKFGSDIIKLLSADMNADVVCHTLEF
CKQNTGQPLCHLYPLPKETWKFTLQKARQIVKKSPILK
YSRSGSDICSLPVLAKICQKIKLAMEQSVPFKDVDSDK
YSVFPTLRGYHWRGRDCNDSDESVYPGRRPNNWDV
HQDSNCNGIWGVDPKDGVPYEKKFCEGSQPRGIILLG
DSAGAHFHISPEWITASQMSLNSFINLPTALTNELDWP
QLSGATGFLDSTVGIKEKSIYLRLWKRNHCNHRDYQNI
SRNGASSRNLKKFIESLSRNKVLDYPAIVIYAMIGNDVC
SGKSDPVPAMTTPEKLYSNVMQTLKHLNSHLPNGSHV
ILYGLPDGTFLWDNLHNRYHPLGQLNKDMTYAQLYSF
LNCLQVSPCHGWMSSNKTLRTLTSERAEQLSNTLKKI
AASEKFTNFNLFYMDFAFHEIIQEWQKRGGQPWQLIE
PVDGFHPNEVALLLLADHFWKKVQLQWPQILGKENPF
NPQIKQVFGDQGGH

Host: Mouse

Reactivity: Human

Applications: WB-Tr
(See our web site product page for detailed applications information)

Protocols: See our web site at http://www.abnova.com/support/protocols.asp or product page for detailed protocols

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 313

Gene Symbol: AOAH

Gene Alias: -

Gene Summary: Acyloxyacyl hydrolase (AOAH) is a 2-subunit lipase which selectively hydrolyzes the secondary (acyloxyacyl-linked) fatty acyl chains from the lipid A region of bacterial endotoxins. AOAH may modulate host inflammatory responses to gram-negative bacterial invasion. The 2 subunits are encoded by a single mRNA. [provided by RefSeq]