

Datasheet

APOC1 purified MaxPab rabbit polyclonal antibody (D01P)

biological validity of some variants has not been determined. [provided by RefSeq]

Catalog Number: H00000341-D01P

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against a full-length human APOC1 protein.

Immunogen: APOC1 (NP_001636.1, 1 a.a. ~ 83 a.a.) full-length human protein.

Sequence:

MRLFLSLPVLVVVLSIVLEGPAPAQGTPDVSSALDKLK
EFGNTLEDKARELISRIKQSELSAKMREWFSETFQKVK
EKLKIDS

Host: Rabbit

Reactivity: Human

Applications: WB-Tr

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 341

Gene Symbol: APOC1

Gene Alias: -

Gene Summary: The protein encoded by this gene is a member of the apolipoprotein C1 family. This gene is expressed primarily in the liver, and it is activated when monocytes differentiate into macrophages. A pseudogene of this gene is located 4 kb downstream in the same orientation, on the same chromosome. This gene is mapped to chromosome 19, where it resides within a apolipoprotein gene cluster. Alternatively spliced transcript variants have been found for this gene, but the