

Datasheet

WBP5 polyclonal antibody

Catalog Number: PAB20561

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against recombinant WBP5.

Immunogen: Recombinant protein corresponding to amino acids of human WBP5.

Sequence:

EGKPENESEPKHEEPPKPEEKPEEEEEKLEEEAKAKGT
FRERLIQSLQEFKEDIHNRHLSNEDMFREVDEIDEIRRV
RNKLIVMRWKVNRN

Host: Rabbit

Reactivity: Human

Applications: IHC-P, WB-Tr

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Purification: Antigen affinity purification

Isotype: IgG

Recommend Usage: Immunohistochemistry

(1:200-1:500)

The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)

Storage Instruction: Store at 4°C. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 51186

Gene Symbol: WBP5

Gene Alias: DKFZp313K1940, TCEAL9

Gene Summary: The globular WW domain is composed of 38 to 40 semiconserved amino acids shared by proteins of diverse functions including structural, regulatory, and signaling proteins. The domain is involved in mediating protein-protein interactions through the binding of polyproline ligands. This gene encodes a WW domain binding protein. This gene also encodes a domain with similarity to the transcription elongation factor A, SII-related family. Alternative splicing results in multiple transcript variants encoding a single isoform. [provided by RefSeq]