

Datasheet

LRMP polyclonal antibody

Catalog Number: PAB21169

Regulation Status: For research use only (RUO)

Product Description: Rabbit polyclonal antibody raised against recombinant LRMP.

Immunogen: Recombinant protein corresponding to amino acids of human LRMP.

Sequence:

RSASLNSKPSSLRRVTIASLPRNIGNAGMVAGMENND
RFSRRSSSWRILGSKQSEHRPSLPRFISTYSWADAE
EKCELKTKDDSEPSGEETVERTRKPSLSEKKNPSKW
DVSSVYD

Host: Rabbit

Reactivity: Human

Applications: IHC-P

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Form: Liquid

Purification: Antigen affinity purification

Isotype: IgG

Recommend Usage: Immunohistochemistry

(1:500-1:1000)

Western Blot (1:250-1:500)

The optimal working dilution should be determined by the end user.

Storage Buffer: In PBS, pH 7.5 (40% glycerol, 0.02% sodium azide)

Storage Instruction: Store at 4°C. For long term storage store at -20°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 4033

Gene Symbol: LRMP

Gene Alias: JAW1

Gene Summary: The protein encoded by this gene is expressed in a developmentally regulated manner in lymphoid cell lines and tissues. The protein is localized to the cytoplasmic face of the endoplasmic reticulum. [provided by RefSeq]