

Datasheet

CKLFSF4 monoclonal antibody (M01), clone 6G4

cluster on chromosome 16. Alternatively spliced transcript variants encoding different isoforms have been identified. [provided by RefSeq]

Catalog Number: H00146223-M01

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody raised against a partial recombinant CKLFSF4.

Clone Name: 6G4

Immunogen: CKLFSF4 (NP_848933, 173 a.a. ~ 234 a.a) partial recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.

Sequence:

QKWRVSVRQQSTNDYIRARTESRDVDSRPEIQRLDTF
SYSTNVTVRKKSPTNLLSLNHWQLA

Host: Mouse

Reactivity: Human

Applications: ELISA, S-ELISA, WB-Ce, WB-Re
(See our web site product page for detailed applications information)

Protocols: See our web site at
<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Isotype: IgG1 Kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 146223

Gene Symbol: CMTM4

Gene Alias: CKLFSF4

Gene Summary: This gene belongs to the chemokine-like factor gene superfamily, a novel family that is similar to the chemokine and the transmembrane 4 superfamilies of signaling molecules. This gene is one of several chemokine-like factor genes located in a