

Datasheet

PSD3 polyclonal antibody

Catalog Number: PAB6499

Regulation Status: For research use only (RUO)

Product Description: Goat polyclonal antibody raised against synthetic peptide of PSD3.

Immunogen: A synthetic peptide corresponding to human PSD3.

Sequence: C-DHRPETPSIKQKVT

Host: Goat

Theoretical MW (kDa): 116, 58.1

Applications: ELISA

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Specificity: This antibody is expected to recognize both reported isoforms (NP_056125.2 NP_996792.1).

Form: Liquid

Purification: Antigen affinity purification

Concentration: 0.5 mg/mL

Recommend Usage: ELISA (1:1000)

The optimal working dilution should be determined by the end user.

Storage Buffer: In Tris saline, pH 7.3 (0.5% BSA, 0.02% sodium azide)

Storage Instruction: Store at -20°C.

Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 23362

Gene Symbol: PSD3

Gene Alias: DKFZp761K1423, EFA6R, HCA67

References:

1. Large scale identification of human hepatocellular carcinoma-associated antigens by autoantibodies. Wang Y, Han KJ, Pang XW, Vaughan HA, Qu W, Dong XY, Peng JR, Zhao HT, Rui JA, Leng XS, Cebon J, Burgess AW, Chen WF. J Immunol. 2002 Jul 15;169(2):1102-9.