

## Datasheet

### WNK1 polyclonal antibody

**Catalog Number:** PAB16444

**Regulation Status:** For research use only (RUO)

**Product Description:** Rabbit polyclonal antibody raised against synthetic peptide of WNK1.

**Immunogen:** A synthetic peptide (conjugated with KLH) corresponding to human WNK1.

**Host:** Rabbit

**Reactivity:**

Bovine, Chicken, Gorilla, Hamster, Horse, Human, Monkey, Mouse, Pig, Rabbit, Rat

**Applications:** IHC-P

(See our web site product page for detailed applications information)

**Protocols:** See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Specificity:** Internal domain of human.

**Form:** Liquid

**Purification:** Immunoaffinity purification

**Recommend Usage:** Immunohistochemistry

(Formalin/PFA-fixed paraffin-embedded sections) (7 ug/mL)

The optimal working dilution should be determined by the end user.

**Storage Buffer:** In PBS (0.1% sodium azide)

**Storage Instruction:** Store at 4°C. For long term storage store at -80°C.

Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 65125

**Gene Symbol:** WNK1

**Gene Alias:** KDP, KIAA0344, PHA2C, PRKWINK1, PSK

**Gene Summary:** The WNK1 gene encodes a cytoplasmic serine-threonine kinase expressed in distal nephron.[supplied by OMIM]