

Datasheet

TNFRSF19L polyclonal antibody (A01)

encoding the same protein have been reported.
[provided by RefSeq]

Catalog Number: H00084957-A01

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a partial recombinant TNFRSF19L.

Immunogen: TNFRSF19L (NP_116260, 26 a.a. ~ 124 a.a) partial recombinant protein with GST tag.

Sequence:

STTLWQCPPGEEPDLDPGQGTLCRPCPPGTFSAAWG
SSPCQPHARCSLWRRLEAQVGMATRD TLCGDCWPG
WFGPWGVPRVPCQPCSWAPLGTHGCDEW

Host: Mouse

Reactivity: Human

Applications: ELISA, WB-Ce, WB-Re

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: 50 % glycerol

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 84957

Gene Symbol: RELT

Gene Alias: FLJ14993, TNFRSF19L

Gene Summary: The protein encoded by this gene is a member of the TNF-receptor superfamily. This receptor is especially abundant in hematologic tissues. It has been shown to activate the NF-kappaB pathway and selectively bind TNF receptor-associated factor 1 (TRAF1). This receptor is capable of stimulating T-cell proliferation in the presence of CD3 signaling, which suggests its regulatory role in immune response. Two alternatively spliced transcript variants of this gene