

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Date of issue: 03/11/2013 Version 1.0

SECTION 1. Identification

Product identifier

Product number 818847

Product name Ethylene glycol dimethacrylate (stabilised with hydroquinone

monomethyl ether) for synthesis

Relevant identified uses of the substance or mixture and uses advised against

Identified uses Chemical for synthesis

Details of the supplier of the safety data sheet

Company EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821,

United States of America | SDS Phone Support: +1-978-715-1335 | General Inquiries: +1-978-715-4321 | Monday to Friday, 9:00 AM to

4:00 PM Eastern Time (GMT-5)

e-mail: mm_sds@merckgroup.com

Emergency telephone 800-424-9300 CHEMTREC (USA)

+1-703-527-3887 CHEMTREC (International)

24 Hours/day; 7 Days/week

SECTION 2. Hazards identification

GHS Classification

Specific target organ systemic toxicity - single exposure, Category 3, H335

Skin sensitization, Category 1, H317

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word Warning

Hazard Statements

H335 May cause respiratory irritation.

H317 May cause an allergic skin reaction.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 818847 Version 1.0

Product name Ethylene glycol dimethacrylate (stabilised with hydroquinone monomethyl ether)

for synthesis

Precautionary Statements

P280 Wear protective gloves.

P302 + P352 IF ON SKIN: Wash with plenty of soap and water.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula $C_{10}H_{14}O_4$ (Hill) CAS-No. 97-90-5 Molar mass 198.22 g/mol

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

ethylene glycol dimethacrylate (>= 90 % - <= 100 %)

97-90-5

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing. Consult a

physician.

Eye contact

After eye contact: rinse out with plenty of water.

Ingestion

After swallowing: caution if victim vomits. Risk of aspiration! Keep airways free. Call a physician immediately. Pulmonary failure possible after aspiration of vomit.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

irritant effects, Allergic reactions, Cough, Shortness of breath

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 818847 Version 1.0

Product name Ethylene glycol dimethacrylate (stabilised with hydroquinone monomethyl ether)

for synthesis

Suitable extinguishing media

Water, Carbon dioxide (CO2), Foam, Dry powder

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible.

Vapors are heavier than air and may spread along floors.

Forms explosive mixtures with air on intense heating.

Development of hazardous combustion gases or vapors possible in the event of fire.

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Do not breathe vapors, aerosols. Avoid substance contact. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent material (e.g. Chemizorb®). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed. Protected from light.

Store at +15°C to +25°C (+59°F to +77°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 818847 Version 1.0

Product name Ethylene glycol dimethacrylate (stabilised with hydroquinone monomethyl ether)

for synthesis

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

protective clothing

Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state liquid

Color colorless

Odor pleasant

Odor Threshold No information available.

pH No information available.

Melting point -20 °C

Boiling point/boiling range 464 °F (240 °C)

at 1,013 hPa

Flash point 214.7 °F (101.5 °C)

Method: DIN 51758

Evaporation rate No information available.

Flammability (solid, gas) No information available.

Lower explosion limit No information available.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 818847 Version 1.0

Product name Ethylene glycol dimethacrylate (stabilised with hydroquinone monomethyl ether)

for synthesis

Upper explosion limit No information available.

Vapor pressure < 1 hPa

at 68 °F (20 °C)

1.3 hPa

at 162 °F (72 °C)

Relative vapor density No information available.

1.05 g/cm³ Relative density

at 68 °F (20 °C)

Water solubility < 5 g/l

at 68 °F (20 °C)

Partition coefficient: n-

log Pow: 1.22

octanol/water (External MSDS) Bioaccumulation is not expected (log Pow

<1).

Autoignition temperature No information available.

Decomposition temperature No information available.

Viscosity, dynamic 3.1 mPa.s

at 68 °F (20 °C)

Explosive properties Not classified as explosive.

SECTION 10. Stability and reactivity

Reactivity

Forms explosive mixtures with air on intense heating.

Chemical stability

heat-sensitive Sensitivity to light

Stabilizer

Hydroquinone monomethyl ether

Possibility of hazardous reactions

Violent reactions possible with:

peroxi compounds, Amines, Heavy metal salts, polymerization initiators

Conditions to avoid

Strong heating.

A range from approx. 15 Kelvin below the flash point is to be rated as critical.

Incompatible materials

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 818847 Version 1.0

Product name Ethylene glycol dimethacrylate (stabilised with hydroquinone monomethyl ether)

for synthesis

no information available

Hazardous decomposition products

no information available

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure Eye contact, Skin contact

Acute oral toxicity

LD50 rat: 3,300 mg/kg (RTECS)

Symptoms: Irritations of mucous membranes in the mouth, pharynx, oesophagus and gastrointestinal tract., Risk of aspiration upon vomiting., Pulmonary failure possible after aspiration of vomit.

Acute inhalation toxicity

Symptoms: mucosal irritations, Cough, Shortness of breath, Possible damages:, damage of respiratory tract

Irritating to respiratory system.

Skin irritation

rabbit

Result: No irritation

FDA 1959 DRAIZE, OCCLUSIV

(External MSDS)

Eye irritation

rabbit

Result: No eye irritation OECD Test Guideline 405

Sensitization

May cause an allergic skin reaction.

Genotoxicity in vitro

Ames test

Salmonella typhimurium

Result: negative

(Lit.)

Specific target organ systemic toxicity - single exposure

May cause respiratory irritation.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC No ingredient of this product present at levels greater than or

equal to 0.1% is identified as probable, possible or confirmed

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 818847 Version 1.0

Product name Ethylene glycol dimethacrylate (stabilised with hydroquinone monomethyl ether)

for synthesis

human carcinogen by IARC.

OSHA No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by OSHA.

NTP No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a known or anticipated carcinogen

by NTP.

ACGIH No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by ACGIH.

Further information

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

Toxicity to fish

LC50 Danio rerio (zebra fish): 15.95 mg/l; 96 h

OECD Test Guideline 203

Toxicity to bacteria

EC50 Pseudomonas putida: 570 mg/l; 3 h

OECD Test Guideline 209

Persistence and degradability

Biodegradability
71 %; 28 d
(External MSDS)
Readily biodegradable.

Bioaccumulative potential

Partition coefficient: n-octanol/water

log Pow: 1.22

(External MSDS) Bioaccumulation is not expected (log Pow <1).

Mobility in soil

No information available.

Other adverse effects

Additional ecological information

Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 818847 Version 1.0

Product name Ethylene glycol dimethacrylate (stabilised with hydroquinone monomethyl ether)

for synthesis

SECTION 14. Transport information

Land transport (DOT)

Not classified as dangerous in the meaning of transport regulations.

Air transport (IATA)

Not classified as dangerous in the meaning of transport regulations.

Sea transport (IMDG)

Not classified as dangerous in the meaning of transport regulations.

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Skin sensitizer

Respiratory irritant

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Acute Health Hazard

SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311,

Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311,

Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

Massachusetts Right To Know

Remarks

No components are subject to the Massachusetts Right to Know Act.

Pennsylvania Right To Know

Ingredients

ethylene glycol dimethacrylate

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 818847 Version 1.0

Product name Ethylene glycol dimethacrylate (stabilised with hydroquinone monomethyl ether)

for synthesis

New Jersey Right To Know

Ingredients

ethylene glycol dimethacrylate

Notification status

TSCA: On TSCA Inventory

DSL: All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H317 May cause an allergic skin reaction. H335 May cause respiratory irritation.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Date of issue:03/11/2013

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.