

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Revision Date 08/20/2013

Version 1.1

SECTION 1. Identification

Product identifier

Product number 112130

Product name Dimidium bromide for surfactant tests

Relevant identified uses of the substance or mixture and uses advised against

analytical reagent. Uses regulated under FDA or FIFRA are not

affected.

Reagent for analysis

Details of the supplier of the safety data sheet

Company EMD Millipore Corporation | 290 Concord Road, Billerica, MA 01821,

United States of America | SDS Phone Support: +1-978-715-1335 | General Inquiries: +1-978-715-4321 | Monday to Friday, 9:00 AM to

4:00 PM Eastern Time (GMT-5)

Emergency telephone 800-424-9300 CHEMTREC (USA)

+1-703-527-3887 CHEMTREC (International)

24 Hours/day; 7 Days/week

SECTION 2. Hazards identification

GHS Classification

Specific target organ systemic toxicity - single exposure, Category 3, H335

Skin irritation, Category 2, H315 Eye irritation, Category 2, H319

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word Warning

Hazard Statements

H315 Causes skin irritation.

H319 Causes serious eye irritation.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 112130 Version 1.1

Product name Dimidium bromide for surfactant tests

H335 May cause respiratory irritation.

Precautionary Statements

P302 + P352 IF ON SKIN: Wash with plenty of soap and water.

P304 + P340 IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula C₂₀H₁₈BrN₃ (Hill)

CAS-No. 518-67-2 Molar mass 380.28 g/mol

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

3,8-diamino-5-methyl-6-phenylphenanthridinium bromide (>= 90 % - <= 100 %)

518-67-2

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact

After eye contact: rinse out with plenty of water. Call in ophthalmologist.

Ingestion

After swallowing: make victim drink water (two glasses at most). Consult doctor if feeling unwell.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

irritant effects, The following applies to aromatic amines in general: systemic effect: methemoglobinemia with headache, cardiac dysrhythmia, drop in blood pressure, dyspnoea, and spasms, principal symptom: cyanosis (blue discoloration of the blood).

Indication of any immediate medical attention and special treatment needed

No information available.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 112130 Version 1.1

Product name Dimidium bromide for surfactant tests

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Water, Carbon dioxide (CO2), Foam, Dry powder

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible material

Development of hazardous combustion gases or vapors possible in the event of fire.

Fire may cause evolution of:

hydrogen bromide, nitrogen oxides

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid inhalation of dusts. Avoid substance contact. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up dry. Dispose of properly. Clean up affected area. Avoid generation of dusts.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed. Dry.

Store at $+5^{\circ}$ C to $+30^{\circ}$ C ($+41^{\circ}$ F to $+86^{\circ}$ F).

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 112130 Version 1.1

Product name Dimidium bromide for surfactant tests

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

protective clothing

Respiratory protection

required when dusts are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	solid

Color red brown

Odor odorless

Odor Threshold No information available.

pH No information available.

Melting point 242 °C

Boiling point No information available.

Flash point No information available.

Evaporation rate No information available.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 112130 Version 1.1

Product name Dimidium bromide for surfactant tests

Flammability (solid, gas) No information available.

Lower explosion limit No information available.

Upper explosion limit No information available.

Vapor pressure No information available.

Relative vapor density No information available.

Relative density No information available.

Water solubility at 68 °F (20 °C)

soluble

Partition coefficient: n-

octanol/water

No information available.

Autoignition temperature No information available.

Decomposition temperature No information available.

Viscosity, dynamic No information available.

Explosive properties Not classified as explosive.

Bulk density ca. 380 kg/m³

SECTION 10. Stability and reactivity

Reactivity

The following applies in general to flammable organic substances and mixtures: in correspondingly fine distribution, when whirled up a dust explosion potential may generally be assumed.

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

Violent reactions possible with:

Strong oxidizing agents

Conditions to avoid

no information available

Incompatible materials

no information available

Hazardous decomposition products

in the event of fire: See section 5.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 112130 Version 1.1

Product name Dimidium bromide for surfactant tests

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact, Ingestion

Acute inhalation toxicity

Symptoms: mucosal irritations, Cough, Shortness of breath, Possible damages:, damage of respiratory tract

Skin irritation

Causes skin irritation.

Eve irritation

Causes serious eye irritation.

Sensitization

Sensitization possible in predisposed persons.

Specific target organ systemic toxicity - single exposure

May cause respiratory irritation.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC No ingredient of this product present at levels greater than or

equal to 0.1% is identified as probable, possible or confirmed

human carcinogen by IARC.

OSHA No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by OSHA.

NTP No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a known or anticipated carcinogen

by NTP.

ACGIH No ingredient of this product present at levels greater than or

equal to 0.1% is identified as a carcinogen or potential

carcinogen by ACGIH.

Further information

Quantitative data on the toxicity of this product are not available.

The following applies to aromatic amines in general: systemic effect: methemoglobinemia with headache, cardiac dysrhythmia, drop in blood pressure, dyspnoea, and spasms, principal symptom: cyanosis (blue discoloration of the blood).

Other dangerous properties can not be excluded.

Handle in accordance with good industrial hygiene and safety practice.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 112130 Version 1.1

Product name Dimidium bromide for surfactant tests

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Additional ecological information

Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number UN 2811

Proper shipping name TOXIC SOLID, ORGANIC, N.O.S. (DIMIDIUM BROMIDE)

Class 6.1
Packing group II
Environmentally hazardous --

Air transport (IATA)

UN number UN 2811

Proper shipping name TOXIC SOLID, ORGANIC, N.O.S. (DIMIDIUM BROMIDE)

Class 6.1
Packing group II
Environmentally hazardous -Special precautions for user no

Sea transport (IMDG)

UN number UN 2811

Proper shipping name TOXIC SOLID, ORGANIC, N.O.S. (DIMIDIUM BROMIDE)

Class 6.1
Packing group II
Environmentally hazardous --

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 112130 Version 1.1

Product name Dimidium bromide for surfactant tests

Special precautions for user yes

EmS F-A S-A

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Skin irritant

Eve irritant

Moderate respiratory irritant

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Acute Health Hazard

SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311,

Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311,

Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

US State Regulations

Massachusetts Right To Know

Remarks

No components are subject to the Massachusetts Right to Know Act.

Pennsylvania Right To Know

Ingredients

3,8-diamino-5-methyl-6-phenylphenanthridinium bromide

New Jersey Right To Know

Ingredients

3,8-diamino-5-methyl-6-phenylphenanthridinium bromide

California Prop 65 Components

This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 112130 Version 1.1

Product name Dimidium bromide for surfactant tests

Notification status

TSCA: Not Listed on TSCA inventory. For Research and Development

Use only. Not For Manufacturing or Commercial Purposes.

Ingredients

3,8-diamino-5-methyl-6-phenylphenanthridinium bromide

DSL: This product contains one or several components that are not on

the Canadian DSL nor NDSL.

Ingredients

3,8-diamino-5-methyl-6-phenylphenanthridinium bromide

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H315 Causes skin irritation.
H319 Causes serious eye irritation.
H335 May cause respiratory irritation.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Revision Date08/20/2013

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.