

Datasheet

APOA1BP purified MaxPab mouse polyclonal antibody (B01P)

[provided by RefSeq]

Catalog Number: H00128240-B01P

Regulation Status: For research use only (RUO)

Product Description: Mouse polyclonal antibody raised against a full-length human APOA1BP protein.

Immunogen: APOA1BP (AAI00933.1, 1 a.a. ~ 185 a.a) full-length human protein.

Sequence:

MSRSPPTVLVICGPGNNGDGLVCARHLKLFGEPTI
YYPKRPNKPLFTALVTQCQKMDIPFLGEMPAEPMIDE
LYELVVDAIFGFSFKGDVREPFHSILSVLKGLTVPIASIDI
PSGWDVEKGNAGGIQPDLLISLTAPKKSATQFTGRYH
YLGGRFVPPALEKKYQLNLPPYPDTECVYRLQ

Host: Mouse

Reactivity: Human

Applications: Det Ab, WB-Tr

(See our web site product page for detailed applications information)

Protocols: See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 128240

Gene Symbol: APOA1BP

Gene Alias: AIBP, MGC119143, MGC119144, MGC119145, YJEFN1

Gene Summary: The product of this gene interacts with apolipoprotein A-I (apoA-I), the major apolipoprotein of high-density lipoproteins (HDLs). It is secreted into some bodily fluids, and its synthesis and secretion are stimulated in vitro by incubating cells with apoA-I. The human genome contains related pseudogenes.