9F, No. 108, Jhouzih St.,Taipei, Taiwan
Tel: + 886-2-8751-1888 Fax: + 886-2-6602-1218
E-mail: sales@abnova.com

Datasheet

C20orf102 monoclonal antibody (M01), clone 3B9

Catalog Number: H00128434-M01

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody raised against a full length recombinant C20orf102.

Clone Name: 3B9

Immunogen: C20orf102 (AAH33818.1, 25 a.a. ~ 204 a.a) full-length recombinant protein with GST tag. MW of the GST tag alone is 26 KDa.

Sequence:
TRPAGHAPWDNHVSGHALFTETPHDMTARTGEDVEM
ACSFRGSGSPSYSLEIQWWYVRSHRDWTDKQAWAS
NQLKASQQEDAGKEATKISVVKVVGSNISHKLRLSRVK
PTDEGSYECRVIDFSDGKARHHKVKAYLRVQPGENSV
LHLPEAPPAAPAPPPPKPGKELRKRSVDQEACSL

Host: Mouse

Reactivity: Human

Applications: ELISA, S-ELISA, WB-Ce, WB-Re, WB-Tr (See our web site product page for detailed applications information)

Protocols: See our web site at http://www.abnova.com/support/protocols.asp or product page for detailed protocols

Isotype: IgG1 Kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

Entrez GeneID: 128434

Gene Symbol: VSTM2L

Gene Alias: C20orf102, dJ1118M15.2

References:
1. EXTRACELLULAR AND MEMBRANE-ASSOCIATED PROSTATE CANCER MARKERS Klee, George G. ;Vasmatzis, George;Kosari, Farhad;Klee, Eric W. FreshPatents.com