

## Datasheet

### ASB10 polyclonal antibody (A01)

**Catalog Number:** H00136371-A01

**Regulation Status:** For research use only (RUO)

**Product Description:** Mouse polyclonal antibody raised against a partial recombinant ASB10.

**Immunogen:** ASB10 (NP\_001135931, 48 a.a. ~ 153 a.a) partial recombinant protein with GST tag.

**Sequence:**

MSWSPEECKGQGEPLDDRHPLCARLVEKPSRGSEEH  
LKSGPGPIVTRTASGPALAFWQAVLAGDVGCVSRLAD  
SSTGLAPDSVFDTSDPERWRDFRFRNIRALRLW

**Host:** Mouse

**Reactivity:** Human

**Applications:** ELISA, WB-Re

(See our web site product page for detailed applications information)

**Protocols:** See our web site at

<http://www.abnova.com/support/protocols.asp> or product page for detailed protocols

**Storage Buffer:** 50 % glycerol

**Storage Instruction:** Store at -20°C or lower. Aliquot to avoid repeated freezing and thawing.

**Entrez GeneID:** 136371

**Gene Symbol:** ASB10

**Gene Alias:** -

**Gene Summary:** The protein encoded by this gene is a member of the ankyrin repeat and SOCS box-containing (ASB) family of proteins. The SOCS box serves to couple suppressor of cytokine signaling (SOCS) proteins and their binding partners with the elongin B and C complex, possibly targeting them for degradation. Multiple alternatively spliced transcript variants have been described for this gene. [provided by RefSeq]