



MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Date of issue: 03/11/2013

Version 1.0

SECTION 1. Identification

Product identifier

Product number	822156
Product name	Tetramethylammonium chloride for synthesis

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Chemical for synthesis
-----------------	------------------------

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America SDS Phone Support: +1-978-715-1335 General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5) e-mail: mm_sds@merckgroup.com
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS Classification

Acute toxicity, Category 2, Oral, H300

Acute toxicity, Category 3, Dermal, H311

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Danger

Hazard Statements

H300 Fatal if swallowed.

H311 Toxic in contact with skin.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 822156
Product name Tetramethylammonium chloride for synthesis

Version 1.0

Precautionary Statements

P280 Wear protective gloves/ protective clothing.

P302 + P352 IF ON SKIN: Wash with plenty of soap and water.

P309 + P310 IF exposed or if you feel unwell: Immediately call a POISON CENTER or doctor/physician.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula	(CH ₃) ₄ NCl	C ₄ H ₁₂ ClN (Hill)
CAS-No.	75-57-0	
Molar mass	109.60 g/mol	

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

tetramethylammonium chloride (>= 90 % - <= 100 %)
75-57-0

SECTION 4. First aid measures

Description of first-aid measures

General advice

First aider needs to protect himself.

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing. Get medical attention.

Eye contact

After eye contact: rinse out with plenty of water with the eyelid held wide open. Call in ophthalmologist if necessary.

Ingestion

If swallowed: give water to drink (two glasses at most). Seek medical advice immediately. In exceptional cases only, if medical care is not available within one hour, induce vomiting (only in persons who are wide awake and fully conscious), administer activated charcoal (20 - 40 g in a 10% slurry) and consult a doctor as quickly as possible.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

Drowsiness, Convulsions

Indication of any immediate medical attention and special treatment needed

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 822156
Product name Tetramethylammonium chloride for synthesis

Version 1.0

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Dry powder, Carbon dioxide (CO₂), Foam, Water

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible.

Development of hazardous combustion gases or vapors possible in the event of fire.

Fire may cause evolution of:

Hydrogen chloride gas, nitrogen oxides

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid substance contact. Avoid inhalation of dusts.

Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up dry. Dispose of properly. Clean up affected area. Avoid generation of dusts.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Dry. Tightly closed. Keep in a well-ventilated place. Keep locked up or in an area accessible only to qualified or authorized persons.

Store at +15°C to +25°C (+59°F to +77°F).

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

822156

Version 1.0

Product name

Tetramethylammonium chloride for synthesis

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

protective clothing

Respiratory protection

required when dusts are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	crystals
Color	colorless
Odor	weakly amine-like
Odor Threshold	No information available.
pH	6 - 8 at 100 g/l 68 °F (20 °C)
Melting point	368 °C
Boiling point	No information available.
Flash point	No information available.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	822156	Version 1.0
Product name	Tetramethylammonium chloride for synthesis	

Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	at 68 °F (20 °C) low
Relative vapor density	No information available.
Relative density	1.17 g/cm ³ at 68 °F (20 °C)
Water solubility	at 68 °F (20 °C) soluble
Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	> 572 °F (> 300 °C)
Viscosity, dynamic	No information available.
Explosive properties	Not classified as explosive.

SECTION 10. Stability and reactivity

Reactivity

The following applies in general to flammable organic substances and mixtures: in correspondingly fine distribution, when whirled up a dust explosion potential may generally be assumed.

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

Violent reactions possible with:
alkalines

Conditions to avoid

no information available

Incompatible materials

no information available

Hazardous decomposition products

in the event of fire: See section 5.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

822156

Version 1.0

Product name

Tetramethylammonium chloride for synthesis

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact, Ingestion

Acute oral toxicity

LD50 rat: 50 mg/kg (RTECS)

absorption

Acute dermal toxicity

LD50 rat: 537 mg/kg

(External MSDS)

absorption

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC

No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.

OSHA

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

NTP

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

ACGIH

No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

After absorption:

Convulsions, Drowsiness

Other dangerous properties can not be excluded.

Handle in accordance with good industrial hygiene and safety practice.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

822156

Version 1.0

Product name

Tetramethylammonium chloride for synthesis

SECTION 12. Ecological information

Ecotoxicity

Toxicity to fish

LC50 Pimephales promelas (fathead minnow): 462 mg/l; 96 h (Lit.)

Persistence and degradability

No information available.

Bioaccumulative potential

No information available.

Mobility in soil

No information available.

Other adverse effects

Additional ecological information

Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number

UN 2811

Proper shipping name

TOXIC SOLID, ORGANIC, N.O.S. (TETRAMETHYLAMMONIUMCHLORIDE)

Class

6.1

Packing group

III

Environmentally hazardous

--

Air transport (IATA)

UN number

UN 2811

Proper shipping name

TOXIC SOLID, ORGANIC, N.O.S. (TETRAMETHYLAMMONIUMCHLORIDE)

Class

6.1

Packing group

III

Environmentally hazardous

--

Special precautions for user

no

Sea transport (IMDG)

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	822156	Version 1.0
Product name	Tetramethylammonium chloride for synthesis	

UN number	UN 2811
Proper shipping name	TOXIC SOLID, ORGANIC, N.O.S. (TETRAMETHYLAMMONIUMCHLORIDE)
Class	6.1
Packing group	III
Environmentally hazardous	--
Special precautions for user	yes
EmS	F-A S-A

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Highly toxic by ingestion

Toxic by skin absorption

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Acute Health Hazard

SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

Massachusetts Right To Know

Remarks

No components are subject to the Massachusetts Right to Know Act.

Pennsylvania Right To Know

Ingredients

tetramethylammonium chloride

New Jersey Right To Know

Ingredients

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

822156

Version 1.0

Product name

Tetramethylammonium chloride for synthesis

tetramethylammonium chloride

Notification status

TSCA:

On TSCA Inventory

DSL:

All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H300

Fatal if swallowed.

H311

Toxic in contact with skin.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Millipore Ref.

1161819995 OP-MUSTER IN G

Date of issue:03/11/2013

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.