



# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Date of issue: 03/11/2013

Version 1.0

## SECTION 1. Identification

### Product identifier

Product number	816122
Product name	O-(1H-6-Chlorobenzotriazol-1-yl)-1,1,3,3- tetramethyluronium hexafluorophosphate for synthesis

### Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Use restricted under TSCA to research and development or as analytical reagent. Uses regulated under FDA or FIFRA are not affected. Chemical for synthesis
-----------------	---

### Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation   290 Concord Road, Billerica, MA 01821, United States of America   SDS Phone Support: +1-978-715-1335   General Inquiries: +1-978-715-4321   Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5)  e-mail: mm_sds@merckgroup.com
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

## SECTION 2. Hazards identification

### GHS Classification

Flammable solid, Category 1, H228

For the full text of the H-Statements mentioned in this Section, see Section 16.

### GHS-Labeling

*Hazard pictograms*



*Signal Word*  
Danger

# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 816122  
Product name O-(1H-6-Chlorobenzotriazol-1-yl)-1,1,3,3- tetramethyluronium  
hexafluorophosphate for synthesis

---

Version 1.0

## *Hazard Statements*

H228 Flammable solid

## *Precautionary Statements*

P210 Keep away from heat.

Caution - substance not yet tested completely.

## **OSHA Hazards**

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

## **Other hazards**

None known.

---

## **SECTION 3. Composition/information on ingredients**

Formula  $C_{11}H_{15}ClF_6N_5OP$  (Hill)

CAS-No. 330645-87-9

Molar mass 413.69 g/mol

Remarks No hazardous ingredients according to the OSHA Hazard Communication Standard 29 CFR 1910.1200.

---

## **SECTION 4. First aid measures**

### **Description of first-aid measures**

#### *Inhalation*

After inhalation: fresh air. Consult doctor if feeling unwell.

#### *Skin contact*

After skin contact: wash off with plenty of water. Remove contaminated clothing.

#### *Eye contact*

After eye contact: rinse out with plenty of water with the eyelid held wide open. Call in ophthalmologist if necessary.

#### *Ingestion*

After swallowing: immediately make victim drink water (two glasses at most). Consult a physician.

Never give anything by mouth to an unconscious person.

### **Most important symptoms and effects, both acute and delayed**

We have no description of any toxic symptoms.

### **Indication of any immediate medical attention and special treatment needed**

No information available.

---

## **SECTION 5. Fire-fighting measures**

### **Extinguishing media**

---

## MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 816122  
Product name O-(1H-6-Chlorobenzotriazol-1-yl)-1,1,3,3- tetramethyluronium  
hexafluorophosphate for synthesis

---

Version 1.0

### *Suitable extinguishing media*

Water, Carbon dioxide (CO<sub>2</sub>), Foam, Dry powder

### *Unsuitable extinguishing media*

For this substance/mixture no limitations of extinguishing agents are given.

### **Special hazards arising from the substance or mixture**

Combustible.

Development of hazardous combustion gases or vapors possible in the event of fire.

Fire may cause evolution of:

Hydrogen fluoride, Hydrogen chloride gas, nitrogen oxides, Oxides of phosphorus

### **Advice for firefighters**

#### *Special protective equipment for fire-fighters*

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

#### *Further information*

Suppress (knock down) gases/vapors/mists with a water spray jet. Prevent fire extinguishing water from contaminating surface water or the ground water system.

---

## **SECTION 6. Accidental release measures**

### **Personal precautions, protective equipment and emergency procedures**

Advice for non-emergency personnel: Avoid substance contact. Avoid inhalation of dusts.

Ensure adequate ventilation. Keep away from open flames, hot surfaces and sources of ignition.

Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

### **Environmental precautions**

Do not empty into drains.

Risk of explosion.

### **Methods and materials for containment and cleaning up**

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up dry. Dispose of properly. Clean up affected area. Avoid generation of dusts.

---

## **SECTION 7. Handling and storage**

### **Precautions for safe handling**

Observe label precautions.

#### *Advice on protection against fire and explosion*

Keep away from open flames, hot surfaces and sources of ignition. Take precautionary measures against static discharge.

### **Conditions for safe storage, including any incompatibilities**

Dry. Tightly closed. Keep away from heat and sources of ignition.

Store at +15°C to +25°C (+59°F to +77°F).

## MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 816122  
Product name O-(1H-6-Chlorobenzotriazol-1-yl)-1,1,3,3- tetramethyluronium  
hexafluorophosphate for synthesis

---

Version 1.0

---

### SECTION 8. Exposure controls/personal protection

#### Exposure limit(s)

Contains no substances with occupational exposure limit values.

#### Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

#### Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

#### Hygiene measures

Change contaminated clothing. Application of skin- protective barrier cream recommended.  
Wash hands after working with substance.

#### Eye/face protection

Safety glasses

#### Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

#### Other protective equipment:

Flame retardant antistatic protective clothing

#### Respiratory protection

required when dusts are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

---

### SECTION 9. Physical and chemical properties

Physical state	solid
Color	white
Odor	No strong odor known.
Odor Threshold	No information available.
pH	No information available.
Melting point	> 185 °C
Boiling point	No information available.
Flash point	No information available.
Evaporation rate	No information available.

---

## MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	816122
Product name	O-(1H-6-Chlorobenzotriazol-1-yl)-1,1,3,3- tetramethyluronium hexafluorophosphate for synthesis

Version 1.0

---

Flammability (solid, gas)	The substance or mixture is a flammable solid with the category 1.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	No information available.
Relative vapor density	No information available.
Relative density	No information available.
Water solubility	No information available.
Partition coefficient: n-octanol/water	No information available.
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.
Explosive properties	Not classified as explosive.

---

### SECTION 10. Stability and reactivity

#### Reactivity

Explosive

The following applies in general to flammable organic substances and mixtures: in correspondingly fine distribution, when whirled up a dust explosion potential may generally be assumed.

#### Chemical stability

heat-sensitive

Sensitivity to light

#### Possibility of hazardous reactions

Violent reactions possible with:

Strong oxidizing agents

#### Conditions to avoid

Strong heating.

#### Incompatible materials

no information available

#### Hazardous decomposition products

in the event of fire: See section 5.

## MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 816122  
Product name O-(1H-6-Chlorobenzotriazol-1-yl)-1,1,3,3- tetramethyluronium  
hexafluorophosphate for synthesis

---

Version 1.0

---

### SECTION 11. Toxicological information

#### Information on toxicological effects

##### *Likely route of exposure*

Eye contact, Skin contact, Ingestion

##### *Specific target organ systemic toxicity - single exposure*

The substance or mixture is not classified as specific target organ toxicant, single exposure.

##### *Specific target organ systemic toxicity - repeated exposure*

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

##### *Aspiration hazard*

Regarding the available data the classification criteria are not fulfilled.

#### Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

#### Further information

Hazardous properties cannot be excluded.

Handle in accordance with good industrial hygiene and safety practice.

---

### SECTION 12. Ecological information

#### Ecotoxicity

No information available.

#### Persistence and degradability

No information available.

#### Bioaccumulative potential

No information available.

#### Mobility in soil

No information available.

#### Other adverse effects

# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 816122  
Product name O-(1H-6-Chlorobenzotriazol-1-yl)-1,1,3,3- tetramethyluronium  
hexafluorophosphate for synthesis

Version 1.0

## SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

## SECTION 14. Transport information

### Land transport (DOT)

UN number UN 1325  
Proper shipping name FLAMMABLE SOLID, ORGANIC, N.O.S. ( O-(1H-6-CHLOROBENZOTRIAZOL--1-YL)-1,1,3,3-TETRAMETHYLURONIUM HEXAFLUOROPHOSPHATE)  
Class 4.1  
Packing group II  
Environmentally hazardous --

### Air transport (IATA)

UN number UN 1325  
Proper shipping name FLAMMABLE SOLID, ORGANIC, N.O.S. ( O-(1H-6-CHLOROBENZOTRIAZOL--1-YL)-1,1,3,3-TETRAMETHYLURONIUM HEXAFLUOROPHOSPHATE)  
Class 4.1  
Packing group II  
Environmentally hazardous --  
Special precautions for user no

### Sea transport (IMDG)

UN number UN 1325  
Proper shipping name FLAMMABLE SOLID, ORGANIC, N.O.S. ( O-(1H-6-CHLOROBENZOTRIAZOL--1-YL)-1,1,3,3-TETRAMETHYLURONIUM HEXAFLUOROPHOSPHATE)  
Class 4.1  
Packing group II  
Environmentally hazardous --  
Special precautions for user yes  
EmS F-A S-G

## SECTION 15. Regulatory information

### United States of America

#### OSHA Hazards

Flammable Solid

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 816122  
Product name O-(1H-6-Chlorobenzotriazol-1-yl)-1,1,3,3- tetramethyluronium hexafluorophosphate for synthesis

---

Version 1.0

## SARA 311/312 Hazards

Fire Hazard

## SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

## SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

## Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

## DEA List I

Not listed

## DEA List II

Not listed

## Massachusetts Right To Know

Remarks

No components are subject to the Massachusetts Right to Know Act.

## Pennsylvania Right To Know

*Ingredients*

O-(1H-6-chlorobenzotriazol-1-yl)-1,1,3,3-tetramethyluroniumhexafluorophosphate

## New Jersey Right To Know

*Ingredients*

O-(1H-6-chlorobenzotriazol-1-yl)-1,1,3,3-tetramethyluroniumhexafluorophosphate

## Notification status

TSCA:

Not Listed on TSCA inventory. For Research and Development Use only. Not For Manufacturing or Commercial Purposes.

*Ingredients*

O-(1H-6-chlorobenzotriazol-1-yl)-1,1,3,3-tetramethyluroniumhexafluorophosphate

DSL:

This product contains one or several components that are not on the Canadian DSL nor NDSL.

*Ingredients*

O-(1H-6-chlorobenzotriazol-1-yl)-1,1,3,3-tetramethyluroniumhexafluorophosphate

---

## SECTION 16. Other information

Training advice



# MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	816122
Product name	O-(1H-6-Chlorobenzotriazol-1-yl)-1,1,3,3- tetramethyluronium hexafluorophosphate for synthesis

---

Version 1.0

Provide adequate information, instruction and training for operators.

**Full text of H-Statements referred to under sections 2 and 3.**

H228 Flammable solid

**Key or legend to abbreviations and acronyms used in the safety data sheet**

Used abbreviations and acronyms can be looked up at [www.wikipedia.org](http://www.wikipedia.org).

Date of issue:03/11/2013

---

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

*All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.*