



MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Date of issue: 03/11/2013

Version 1.0

SECTION 1. Identification

Product identifier

Product number	818071
Product name	Hexamethyltriaminophosphine for synthesis

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Chemical for synthesis
-----------------	------------------------

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America SDS Phone Support: +1-978-715-1335 General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5) e-mail: mm_sds@merckgroup.com
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS Classification

Flammable liquid, Category 3, H226

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word
Warning

Hazard Statements
H226 Flammable liquid and vapor.

Precautionary Statements
P210 Keep away from heat.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 818071
Product name Hexamethyltriaminophosphine for synthesis

Version 1.0

P262 Do not get in eyes, on skin, or on clothing.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula	P[N(CH ₃) ₂] ₃	C ₆ H ₁₈ N ₃ P (Hill)
CAS-No.	1608-26-0	
Molar mass	163.2 g/mol	

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

hexamethyltriaminophosphine (>= 90 % - <= 100 %)

1608-26-0

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact

After eye contact: rinse out with plenty of water.

Ingestion

After swallowing: make victim drink water (two glasses at most). Consult doctor if feeling unwell.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

We have no description of any toxic symptoms.

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Carbon dioxide (CO₂), Dry powder, Foam

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 818071
Product name Hexamethyltriaminophosphine for synthesis

Version 1.0

Combustible.
Vapors are heavier than air and may spread along floors.
Forms explosive mixtures with air at elevated temperatures.
Pay attention to flashback.
Development of hazardous combustion gases or vapors possible in the event of fire.
Fire may cause evolution of:
Oxides of phosphorus, nitrogen oxides, phosphines

Advice for firefighters

Special protective equipment for fire-fighters
In the event of fire, wear self-contained breathing apparatus.

Further information

Prevent fire extinguishing water from contaminating surface water or the ground water system.
Suppress (knock down) gases/vapors/mists with a water spray jet. Remove container from danger zone and cool with water.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Do not breathe vapors, aerosols. Keep away from heat and sources of ignition. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains. Risk of explosion.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.
Observe possible material restrictions (see sections 7 and 10).
Take up with liquid-absorbent material (e.g. Chemisorb®). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Advice on protection against fire and explosion

Keep away from open flames, hot surfaces and sources of ignition. Take precautionary measures against static discharge.

Conditions for safe storage, including any incompatibilities

Keep away from heat and sources of ignition. Keep container tightly closed in a dry and well-ventilated place.

Store at +15°C to +25°C (+59°F to +77°F).

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

818071

Version 1.0

Product name

Hexamethyltriaminophosphine for synthesis

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Change contaminated clothing. Application of skin- protective barrier cream recommended.

Wash hands after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

Flame retardant antistatic protective clothing

Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless
Odor	unpleasant
Odor Threshold	No information available.
pH	No information available.
Melting point	-44 °C
Boiling point/boiling range	324 - 327 °F (162 - 164 °C) at 1,013 mbar
Flash point	81 °F (27 °C) Method: c.c.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	818071	Version 1.0
Product name	Hexamethyltriaminophosphine for synthesis	

Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.
Vapor pressure	3.72 hPa at 68 °F (20 °C)
Relative vapor density	No information available.
Relative density	0.90 g/cm ³ at 68 °F (20 °C)
Water solubility	at 68 °F (20 °C) (slow decomposition)
Partition coefficient: n-octanol/water	log Pow: 1.70 (calculated) Bioaccumulation is not expected (log Pow <1). (Lit.)
Autoignition temperature	No information available.
Decomposition temperature	No information available.
Viscosity, dynamic	No information available.
Explosive properties	Not classified as explosive.

SECTION 10. Stability and reactivity

Reactivity

Vapor/air-mixtures are explosive at intense warming.

Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

Possibility of hazardous reactions

Violent reactions possible with:

Oxidizing agents

Conditions to avoid

Heating.

A range from approx. 15 Kelvin below the flash point is to be rated as critical.

Exposure to moisture.

Incompatible materials

no information available

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

818071

Version 1.0

Product name

Hexamethyltriaminophosphine for synthesis

Hazardous decomposition products

in the event of fire: See section 5.

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Inhalation, Eye contact, Skin contact

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

Hazardous properties cannot be excluded but are unlikely when the product is handled appropriately.

Handle in accordance with good industrial hygiene and safety practice.

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

Partition coefficient: n-octanol/water

log Pow: 1.70

(calculated)

Bioaccumulation is not expected (log Pow <1). (Lit.)

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

818071

Version 1.0

Product name

Hexamethyltriaminophosphine for synthesis

Mobility in soil

No information available.

Other adverse effects

Additional ecological information

Biological effects:

Product reacts with water.

Depending on the concentration, phosphorus and/or nitrogen compounds may contribute to the eutrophication of drinking- water supplies.

Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number

UN 1993

Proper shipping name

FLAMMABLE LIQUID, N.O.S. (HEXAMETHYLTRIAMINOPHOSPHINE)

Class

3

Packing group

III

Environmentally hazardous

--

Air transport (IATA)

UN number

UN 1993

Proper shipping name

FLAMMABLE LIQUID, N.O.S. (HEXAMETHYLTRIAMINOPHOSPHINE)

Class

3

Packing group

III

Environmentally hazardous

--

Special precautions for user

no

Sea transport (IMDG)

UN number

UN 1993

Proper shipping name

FLAMMABLE LIQUID, N.O.S. (HEXAMETHYLTRIAMINOPHOSPHINE)

Class

3

Packing group

III

Environmentally hazardous

--

Special precautions for user

yes

EmS

F-E S-D

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number

818071

Version 1.0

Product name

Hexamethyltriaminophosphine for synthesis

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Flammable Liquid

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Fire Hazard

SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

Massachusetts Right To Know

Remarks

No components are subject to the Massachusetts Right to Know Act.

Pennsylvania Right To Know

Ingredients

hexamethyltriaminophosphine

New Jersey Right To Know

Ingredients

hexamethyltriaminophosphine

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 818071
Product name Hexamethyltriaminophosphine for synthesis

Version 1.0

Notification status

TSCA: On TSCA Inventory

DSL: All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H226 Flammable liquid and vapor.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Date of issue:03/11/2013

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.