



MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Date of issue: 03/11/2013

Version 1.0

SECTION 1. Identification

Product identifier

Product number	818677
Product name	Lauraldehyde for synthesis

Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Chemical for synthesis
-----------------	------------------------

Details of the supplier of the safety data sheet

Company	EMD Millipore Corporation 290 Concord Road, Billerica, MA 01821, United States of America SDS Phone Support: +1-978-715-1335 General Inquiries: +1-978-715-4321 Monday to Friday, 9:00 AM to 4:00 PM Eastern Time (GMT-5) e-mail: mm_sds@merckgroup.com
---------	--

Emergency telephone	800-424-9300 CHEMTREC (USA) +1-703-527-3887 CHEMTREC (International) 24 Hours/day; 7 Days/week
---------------------	--

SECTION 2. Hazards identification

GHS Classification

Skin irritation, Category 2, H315

Chronic aquatic toxicity, Category 2, H411

For the full text of the H-Statements mentioned in this Section, see Section 16.

GHS-Labeling

Hazard pictograms



Signal Word

Warning

Hazard Statements

H315 Causes skin irritation.

H411 Toxic to aquatic life with long lasting effects.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 818677
Product name Lauraldehyde for synthesis

Version 1.0

Precautionary Statements

P273 Avoid release to the environment.

P302 + P352 IF ON SKIN: Wash with plenty of soap and water.

OSHA Hazards

This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Other hazards

None known.

SECTION 3. Composition/information on ingredients

Formula	$\text{CH}_3(\text{CH}_2)_{10}\text{CHO}$	$\text{C}_{12}\text{H}_{24}\text{O}$ (Hill)
CAS-No.	112-54-9	
Molar mass	184.32 g/mol	

Hazardous ingredients

Chemical Name (Concentration)

CAS-No.

dodecanal (>= 90 % - <= 100 %)

112-54-9

SECTION 4. First aid measures

Description of first-aid measures

Inhalation

After inhalation: fresh air.

Skin contact

After skin contact: wash off with plenty of water. Remove contaminated clothing.

Eye contact

After eye contact: rinse out with plenty of water.

Ingestion

After swallowing: immediately make victim drink water (two glasses at most). Consult a physician.

Never give anything by mouth to an unconscious person.

Most important symptoms and effects, both acute and delayed

irritant effects

The following applies to aldehydes in general: irritations after contact with eyes and skin.
Mucosal irritations, coughing, and dyspnoea after inhalation.

Indication of any immediate medical attention and special treatment needed

No information available.

SECTION 5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media

Carbon dioxide (CO₂), Foam, Dry powder

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 818677
Product name Lauraldehyde for synthesis

Version 1.0

Unsuitable extinguishing media

For this substance/mixture no limitations of extinguishing agents are given.

Special hazards arising from the substance or mixture

Combustible.

Vapors are heavier than air and may spread along floors.

Forms explosive mixtures with air on intense heating.

Development of hazardous combustion gases or vapors possible in the event of fire.

Advice for firefighters

Special protective equipment for fire-fighters

Stay in danger area only with self-contained breathing apparatus. Prevent skin contact by keeping a safe distance or by wearing suitable protective clothing.

Further information

Prevent fire extinguishing water from contaminating surface water or the ground water system.

SECTION 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Advice for non-emergency personnel: Avoid substance contact. Do not breathe vapors, aerosols. Ensure adequate ventilation. Evacuate the danger area, observe emergency procedures, consult an expert.

Advice for emergency responders: Protective equipment see section 8.

Environmental precautions

Do not empty into drains.

Methods and materials for containment and cleaning up

Cover drains. Collect, bind, and pump off spills.

Observe possible material restrictions (see sections 7 and 10).

Take up with liquid-absorbent material (e.g. Chemizorb®). Dispose of properly. Clean up affected area.

SECTION 7. Handling and storage

Precautions for safe handling

Observe label precautions.

Conditions for safe storage, including any incompatibilities

Tightly closed. Protected from light.

Store at +2°C to +8°C (+36°F to +46°F).

SECTION 8. Exposure controls/personal protection

Exposure limit(s)

Contains no substances with occupational exposure limit values.

Engineering measures

Technical measures and appropriate working operations should be given priority over the use of personal protective equipment.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 818677
Product name Lauraldehyde for synthesis

Version 1.0

Individual protection measures

Protective clothing should be selected specifically for the workplace, depending on concentration and quantity of the hazardous substances handled. The chemical resistance of the protective equipment should be inquired at the respective supplier.

Hygiene measures

Immediately change contaminated clothing. Apply skin- protective barrier cream. Wash hands and face after working with substance.

Eye/face protection

Safety glasses

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Other protective equipment:

protective clothing

Respiratory protection

required when vapors/aerosols are generated.

Use a properly fitted, air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.

SECTION 9. Physical and chemical properties

Physical state	liquid
Color	colorless
Odor	characteristic
Odor Threshold	No information available.
pH	No information available.
Melting point	11 - 13 °C
Boiling point/boiling range	459 - 462 °F (237 - 239 °C) at 1,013 hPa
Flash point	214 °F (101 °C)
Evaporation rate	No information available.
Flammability (solid, gas)	No information available.
Lower explosion limit	No information available.
Upper explosion limit	No information available.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	818677	Version 1.0
Product name	Lauraldehyde for synthesis	

Vapor pressure	< 300 hPa at 122 °F (50 °C)
Relative vapor density	No information available.
Relative density	0.83 g/cm ³ at 68 °F (20 °C)
Water solubility	at 68 °F (20 °C) practically insoluble
Partition coefficient: n-octanol/water	log Pow: 4.75 (calculated) (Lit.) Potential bioaccumulation
Autoignition temperature	No information available.
Decomposition temperature	> 212 °F (> 100 °C)
Viscosity, dynamic	No information available.
Explosive properties	Not classified as explosive.
Ignition temperature	392 °F (200 °C)

SECTION 10. Stability and reactivity

Reactivity

Forms explosive mixtures with air on intense heating.

Chemical stability

Sensitivity to light

Sensitive to air.

Possibility of hazardous reactions

Violent reactions possible with:

Strong oxidizing agents, Bases, acids

Conditions to avoid

Strong heating.

A range from approx. 15 Kelvin below the flash point is to be rated as critical.

Incompatible materials

no information available

Hazardous decomposition products

no information available

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 818677
Product name Lauraldehyde for synthesis

Version 1.0

SECTION 11. Toxicological information

Information on toxicological effects

Likely route of exposure

Eye contact, Skin contact

Acute oral toxicity

LD50 rat: 23,000 mg/kg (RTECS)

Acute inhalation toxicity

Symptoms: Possible damages: mucosal irritations

Skin irritation

Causes skin irritation.

Eye irritation

Possible damages: slight irritation

Specific target organ systemic toxicity - single exposure

The substance or mixture is not classified as specific target organ toxicant, single exposure.

Specific target organ systemic toxicity - repeated exposure

The substance or mixture is not classified as specific target organ toxicant, repeated exposure.

Aspiration hazard

Regarding the available data the classification criteria are not fulfilled.

Carcinogenicity

IARC	No ingredient of this product present at levels greater than or equal to 0.1% is identified as probable, possible or confirmed human carcinogen by IARC.
OSHA	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.
NTP	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.
ACGIH	No ingredient of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

Further information

The following applies to aldehydes in general: irritations after contact with eyes and skin.

Mucosal irritations, coughing, and dyspnoea after inhalation.

Other dangerous properties can not be excluded.

Handle in accordance with good industrial hygiene and safety practice.

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 818677
Product name Lauraldehyde for synthesis

Version 1.0

SECTION 12. Ecological information

Ecotoxicity

No information available.

Persistence and degradability

No information available.

Bioaccumulative potential

Partition coefficient: n-octanol/water

log Pow: 4.75

(calculated)

(Lit.) Potential bioaccumulation

Mobility in soil

No information available.

Other adverse effects

Additional ecological information

Discharge into the environment must be avoided.

SECTION 13. Disposal considerations

The information presented only applies to the material as supplied. The identification based on characteristic(s) or listing may not apply if the material has been used or otherwise contaminated. It is the responsibility of the waste generator to determine the toxicity and physical properties of the material generated to determine the proper waste identification and disposal methods in compliance with applicable regulations. Disposal should be in accordance with applicable regional, national and local laws and regulations.

SECTION 14. Transport information

Land transport (DOT)

UN number UN 3082

Proper shipping name ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID,
N.O.S. (LAURALDEHYDE)

Class 9

Packing group III

Environmentally hazardous --

Air transport (IATA)

UN number UN 3082

Proper shipping name ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID,
N.O.S. (LAURALDEHYDE)

Class 9

Packing group III

Environmentally hazardous --

Special precautions for user no

Sea transport (IMDG)

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number	818677	Version 1.0
Product name	Lauraldehyde for synthesis	

UN number	UN 3082
Proper shipping name	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (LAURALDEHYDE)
Class	9
Packing group	III
Environmentally hazardous	--
Special precautions for user	yes
EmS	F-A S-F

SECTION 15. Regulatory information

United States of America

OSHA Hazards

Skin irritant

This information is based on 29 CFR 1910.1200 criteria prior to adoption of the GHS, and may deviate from the GHS information on the label and in section 2.

SARA 311/312 Hazards

Acute Health Hazard

SARA 313

SARA 313: This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

SARA 302

SARA 302: No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

Clean Water Act

This product does not contain any Hazardous Substances listed under the U.S. CleanWater Act, Section 311, Table 116.4A.

This product does not contain any Hazardous Chemicals listed under the U.S. CleanWater Act, Section 311, Table 117.3.

DEA List I

Not listed

DEA List II

Not listed

Massachusetts Right To Know

Remarks

No components are subject to the Massachusetts Right to Know Act.

Pennsylvania Right To Know

Ingredients

dodecanal

New Jersey Right To Know

Ingredients

dodecanal

MATERIAL SAFETY DATA SHEET

according to the (US) Hazard Communication Standard (29 CFR 1910.1200)

Product number 818677
Product name Lauraldehyde for synthesis

Version 1.0

Notification status

TSCA: On TSCA Inventory

DSL: All components of this product are on the Canadian DSL.

SECTION 16. Other information

Training advice

Provide adequate information, instruction and training for operators.

Full text of H-Statements referred to under sections 2 and 3.

H315 Causes skin irritation.
H411 Toxic to aquatic life with long lasting effects.

Key or legend to abbreviations and acronyms used in the safety data sheet

Used abbreviations and acronyms can be looked up at www.wikipedia.org.

Date of issue:03/11/2013

The information contained herein is based on the present state of our knowledge. It characterizes the product with regard to appropriate safety precautions. It does not represent a warranty of any product properties and we assume no liability for any loss or injury which may result from the use of this information. Users should conduct their own investigations to determine the suitability of the information.

All rights reserved. Millipore and the "M" Mark are registered trademarks of Merck KGaA, Darmstadt, Germany.